

EDGE™ Field-Term Cassette 12F, LC duplex, Single-mode UPC, No Pigtail

CORNING

Part Number:
EDGE-CS12-AE

EDGE™ Field-term Cassettes provide the interface between the trunk cable and the LC duplex jumpers that connect directly into the electronics. The LC duplex adapters feature hinged VFL-compatible shutters that move up and out of the way when the connector is inserted. The field-term cassette contains no pigtail, but allows for field termination of bulk cables directly into the rear side of the LC duplex adapters using UniCams or anaerobic connectors. This cassette may also be used with preterminated LC trunks.



EDGE™ Field-Term Cassette, 12F, LC duplex, Single-mode UPC

EDGE™ Field-Term Cassette 12F, LC duplex, Single-mode UPC, No Pigtail

CORNING

Specifications

General Specifications

Product Type	Cassettes
Fiber Category	Single-mode (OS2)
Splice option	Yes
Application	Data Center

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Fiber Count	12
Splice Tray Type	EDGE™ splice field-term cassette
Number of Splice Trays	1
Adapter Color Front	Blue
Adapter Type Front	Shuttered LC
Polish	UPC
Housing Type	EDGE
Panel or Module Type	EDGE
Fiber Capacity	12
Number of Adapters per Panel	6

Design - Adapter

Housing Color	Blue
Housing Material	Composite
Keyed adapter	No
Shuttered adapter	Yes
Adapter Type	LC Duplex Shuttered

EDGE™ Field-Term Cassette 12F, LC duplex, Single-mode UPC, No Pigtail

CORNING

Design - Adapter

Insert	Ceramic
--------	---------

Connector Specs

Polish	UPC
--------	-----

Dimensions

Height	25 mm
Width	247 mm
Depth	135 mm
Weight	0.07 kg

Shipping Dimensions

Height	25 mm
Width	247 mm
Depth	135 mm

Ordering Information

Product Number	EDGE-CS12-AE
Module Capacity	12
Shipping Weight	0.12 kg
Shipping Height	25 mm
Shipping Width	247 mm
Shipping Depth	135 mm
Units per Delivery	1/1

EDGE™ Field-Term Cassette 12F, LC duplex, Single-mode UPC, No Pigtail

The Corning logo consists of a solid blue square. Inside the square, the word "CORNING" is written in a white, serif, all-caps font, centered horizontally and vertically.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.