

No Polish Connectors Plus (NPC+) SC/OM2/250/900

CORNING

Part Number: NPCP-SC-OM2-48

The No Polish Connector Plus (NPC+™) is Corning's fastest and simplest field-installable fibre connector, designed to deliver reliable optical performance with minimal tools and training. Featuring a factory-polished end face and a toolless mechanical splice design, NPC+ enables technicians to achieve consistent, high-quality terminations in seconds—without field polishing, fusion splicing, or proprietary installation tools. Engineered for speed, simplicity, and performance, NPC+ is ideal for drop repairs, restoration work, and on-demand fibre terminations wherever an SC or LC connector footprint is required.

Features and Benefits

Installs in less than 10 seconds after cleaving fiber

Minimizes installation time and accelerates service turn-up

Tool-less connector activation

Uses only standard fiber preparation tools, reduces crew tooling cost and simplifies field deployment

Audible and tactile “click” feedback

Provides immediate confirmation of proper termination

Supports both 250 µm and 900 µm fibers

Enables use across a range of fiber and cable types

Single-reuse capability

Allows deactivation of the splice element and strain relief without additional tools



No Polish Connectors Plus, (NPC+) SC/OM2/250/900

No Polish Connectors Plus (NPC+) SC/OM2/250/900



Specifications

General Specifications	
Product type	Field-Installable Connectors
Fibre category	50 µm MM (OM2)
Technology	No-epoxy/no-polish

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	Passed TIA / EIA-568-D.3

Environmental Conditions	
Temperature range, operation	-10 °C to 60 °C
Temperature range, storage	-40 °C to 85 °C

Design - Connector	
Connector type	SC
Housing colour	Black
Ferrule material	Yttria-stabilized Zirconia

Mechanical Specifications - Connector	
Nominal fibre outer diameter	125 µm
Durability	≤ 0.2 dB change, 500 rematings, FOTP-21

Optical Specifications - Connector	
Polish	UPC
Insertion loss, max.	0.5 dB
Reflectance, typical	< -30 dB

No Polish Connectors Plus (NPC+) SC/OM2/250/900



Ordering Information	
Product Number	NPCP-SC-OM2-48
Package contents	48 piece box (6 connectors packaged in plastic thermoformed containers, 8 containers per box). Minimum Order Quantity: 48 PCE
Units per delivery	48/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.