

Cable Prep Tools Fibrlok™ II Universal Optical Fiber Splice, Bulk 2529-B Splicing Tool

The logo consists of a solid blue square with the word "CORNING" written in white, uppercase, serif font centered within it.

CORNING

Part Number:
80611159122

Cable Prep Tools Fibrlok™ II Universal Optical Fiber Splice, Bulk 2529-B Splicing Tool



Specifications

General Specifications	
Product Type	Splice-Toolkit
Environment	Indoor/Outdoor
Cable Diameter	125 mm

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Design	
Fiber Type	250 or 900 μ m
Cable Diameter	125 mm

Optical Specifications - Connector	
Insertion Loss, Typical	0.1 dB

Dimensions	
Depth	381 mm

Ordering Information	
Product Number	80611159122
Units per Delivery	1000/1

Cable Prep Tools Fibrlok™ II Universal Optical Fiber Splice, Bulk 2529-B Splicing Tool

CORNING



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.