

Pretium® Connector Housing (PCH) 2 rack unit, holds 4 CCHE Panels + MFT Tray holder with 4 MFT Trays capacity



CORNING

Part Number:
PCH-02U-SPL

The rack-mount Pretium® connector housings (PCH) are available in 1U, 2U and 4U sizes and mount in 19-in racks or cabinets. Combined with the modules, panels, harnesses, trunks and patch cords, they provide a tip-to-tip solution for your fiber optic network.

Features and Benefits

Compatible with Plug & Play™ Systems modules

Designed to support Plug & Play™ Systems applications

Splice in the housing

Saves rack space and the cost of the second housing

Removable top (1U, 2U)

Maximizes ease of access

Transparent front door (04U and 02U)

Permits viewing while protecting installed patch cords

Large removable fiber guides in front

Effectively manage high patch cord densities

Pretium® Connector Housing (PCH) 2 rack unit, holds 4 CCHE Panels + MFT Tray holder with 4 MFT Trays capacity

CORNING

Specifications

General Specifications

Product Type	Housings
Access Type	Front access fixed
Mounting Type	Rack-mount
Application	Data Center, Enterprise Networks

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
UL-Listed	United States and Canadian safety standards

Design

Lockable	Yes
Splice Tray Type	MFT
Cable entry type	Slotted
Housing Type	PCH
Number of Panels per Housing	4
Panel or Module Type	CCH
Splice Tray Options	6 category 2R, 2S, 2S long, 3 category 4R, 4S, 4S wide
Fiber Capacity	Up to 48 fibers installing FC/SC/ ST® compatible connectors, or up to 96 installing LC connectors
Lock Position	Front or rear

Design - Adapter

Housing Color	Gray
---------------	------

Dimensions

Height	89 mm
--------	-------

Pretium® Connector Housing (PCH) 2 rack unit, holds 4 CCHE Panels + MFT Tray holder with 4 MFT Trays capacity

CORNING

Dimensions

Weight	5.9 kg
--------	--------

Ordering Information

Product Number	PCH-02U-SPL
Height Unit	2 U
Package Contents	Housing; Installation Guide; 4 blank panels; unit ID label; 2 port identification labels for 2 panels; 3 #6-32 x .25 screws; 8 #10-32 x 50 screws; 4 #12-24 x 50 screws; 8 1/8 x 4-in tie wraps, white; spiral wrap, 2 ft; central member strain-relief clamp kit; bracket for mounting UCC clamp; universal cable clamp (UCC) kit with 5 cable inserts; double-sided hook and loop strap, 5/8-in; bracket to hold BTF kit; 2 #6-32, SS nylon self-locking hex nut
Shipping Weight	9.5 kg
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.