


EDGE™ Housing 2 rack unit, Gray, holds up to 24 EDGE modules or panels



**Part Number:
EDGE-02U**

EDGE™ housings are high-density, preterminated fibre optic hardware solutions. They offer industry-leading connector density and easy finger/toolless access to enable faster moves, adds, and changes (MACs). The units can be configured to accommodate 96, 144, 288, or 576 fibers.

EDGE housings can be rack- or cabinet-mounted and are ideal for data centers, local area network (LAN) and storage area network (SAN) applications, as well as enterprise networks.



EDGE™ Housing 2 rack unit, Gray, holds up to 24 EDGE modules or panels



EDGE™ Housing, 2 rack unit, holds up to 24 EDGE modules or panels



EDGE™ Housing, 2 rack unit, holds up to 24 EDGE modules or panels

Specifications

General Specifications

Product Type	Housings
Access Type	Front and rear access slidable
Mounting Type	Rack-mount, Cabinet-mount
Application	Data Center, Enterprise Networks

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Lockable	Yes
Number of Modules	24
Cable entry type	Side brush entry
Number of Panels/Cassettes per Housing	24

EDGE™ Housing 2 rack unit, Gray, holds up to 24 EDGE modules or panels



Design	
Cable Entry Direction	Rear
Housing Type	EDGE
Color	Silver
Panel or Cassette Type	EDGE
Panel or Module Type	EDGE
Fiber Capacity	288
Lock Position	Rear

Design - Adapter	
Housing Color	Silver

Dimensions	
Height	88 mm (3.46 in)
Width	432 mm (17.01 in)
Depth	561 mm (22.09 in)
Weight	8.6 kg

Ordering Information	
Product Number	EDGE-02U
Module Capacity	24
Height Unit	2 U
Trunk Capacity	24 (size 1 or 2, double stack cradle)
Package Contents	EDGE™ Housing 2U; Quick Start Guide, #12-24 and #10-32 mounting screws, Cage Nut Mounting Kit, Velcro Strap, Fiber Optic Warning Label
Shipping Weight	10.9 kg
Shipping Height	216 mm (8.5 in)
Shipping Width	565 mm (22.24 in)

EDGE™ Housing 2 rack unit, Gray, holds up to 24 EDGE modules or panels



Ordering Information	
Shipping Depth	660 mm (25.98 in)
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.