

MDU Terminals, Stubless 12 port, SC UPC, stubless, Internal Optitip® pinned, no drop pigtails

The Corning logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font.

Part Number:
MDU0000123C-00M22Q

The OptiSheath® MDU Terminal is a rugged, indoor/outdoor interconnect between the distribution network and indoor/outdoor drop cables for multidwelling unit (MDU) applications. Compatible with either loose tube or ribbon cable, the terminal also accommodates ClearCurve® Rugged Drop Cable. The multilayer design allows installers to access only the components of the terminal necessary for initial installation or subscriber turn-up, while a protected layer allows for pigtail splicing of drop cables as needed. The NID-like housing contains 6-, 12-, 24- and 48-ports and has built-in mounting provisions for a variety of interior and exterior surfaces, including uneven siding.

Features and Benefits

Available with or without SC pigtails

Allows splicing in field or direct termination in both preconnectorized or field-connectorized drops

Labeled and tiered subscriber ports with dedicated parking

Craft-friendly with easy access

Flame-retardant, impact-resistant engineering-grade thermoplastic and hinged cover with padlock

Maximum product lifetime and security

Flexible design with multiple stub and drop options including an OptiTip® Adapter distribution interface

Provides solutions for a variety of MDU installations

MDU Terminals, Stubless 12 port, SC UPC, stubless, Internal Optitip® pinned, no drop pigtails

CORNING

Specifications

General Specifications

Product Type	MDU Terminals
Fiber Category	Single-mode (OS2)
Application	Multidwelling Unit (MDU)

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Compliance	Not Available

Design

Lockable	Yes
Housing Material	Thermoplastic
Adapter Type Master Level	SC UPC
Adapter Color Front	Blue
Cable Entry Direction	Bottom-Left
Drop Connection	Preconnectorized drops
Input Cable Type	Internal OptiTip, Pinned
Color	Almond
Number of Ports	12

Connector Specs

Ferrule Material	Ceramic
------------------	---------

Specifications - Connector A

Connector Type	SC
Polish	APC

MDU Terminals, Stubless 12 port, SC UPC, stubless, Internal Optitip® pinned, no drop pigtails

CORNING

Dimensions

Height	414 mm (16.3 in)
Width	37.1 mm (1.46 in)
Depth	152 mm (5.98 in)

Ordering Information

Product Number	MDU0000123C-00M22Q
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.