

EDGE8® Housing, FX Fixed, fiber zone box, 4-rack units, holds 48 EDGE8 Solutions modules or panels

CORNING

Part Number:
EDGE8-FZB-04U

EDGE8® FX housings are available in 1U, 2U, and 4U which mounts in 19-in racks or cabinets. Combine these housings with the EDGE8 modules, panels, trunks, harnesses and jumpers to experience an industry-leading solution. The reduced depth of the FX rack-mount housings allow for the back-to-back installation in 4-post racks or cabinets as well as third-party floor boxes.

Features and Benefits

Universal wired components

Enable moves, adds and changes without polarity concerns; provide a simple migration path between 2-fibre and parallel optic applications



EDGE8® Housing, FX Fixed, fiber zone box, 4-rack units, holds 48 EDGE8 Solutions modules or panels

CORNING

Specifications

General Specifications

Product Type	Housings
Application	Data Center

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Fiber Density per Unit	384
Housing Type	EDGE8® Fixed
Number of Panels per Housing	48
Panel or Module Type	EDGE

Dimensions

Height	241 mm
Width	527 mm
Depth	527 mm

Ordering Information

Product Number	EDGE8-FZB-04U
Shipping Weight	18 kg
Shipping Height	356 mm
Shipping Width	656 mm
Shipping Depth	643 mm
Units per Delivery	1/1

EDGE8® Housing, FX Fixed, fiber zone box, 4-rack units, holds 48 EDGE8 Solutions modules or panels

The Corning logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font.

Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.