

12-Fiber MTP® PRO Jumper 12F, Bend-Improved single-mode (OS2), 10 ft

CORNING

Part Number:
J898912GE8-NA010F

EDGE™ MTP® PRO patch cords are used to create a connection between MTP adapter panels, conversion modules, and electronics, typically providing connectivity within the rack or the row. These cable assemblies feature a smaller (2.0 mm) outside diameter than traditional 12-fiber patch cords to improve finger access and reduce congestion and increase airflow in the horizontal and vertical rack space. EDGE 12-fiber MTP patch cords have the same connector size and cable footprint as LC duplex patch cords used today. The density, airflow, and cable management advantages of EDGE solutions was preserved as you migrate to higher data rates.

These patch cords are manufactured using Corning® CleanAdvantage™ technology and shipped with optimized dust caps, eliminating the need for cleaning and scoping prior to the initial field connection. They are built with MTP PRO push-pull connectors, allowing for a simple one-step color-coded polarity change without removing the connector housing. The connector also provides the capability for field-friendly pinning configuration changes with safe handling of pins and easy color identification while maintaining product integrity.

Features and Benefits

Slim round 2-fiber interconnect cable

Improves airflow and reduces congestion

MTP® PRO connectors

Allows for pinning and polarity changes in the field

Bend-improved fiber

Allows tighter cable bends for slack storage and routing, less risk of downtime due to pinched or bent cables

Corning® CleanAdvantage™ technology and optimized dust cap

Eliminates the need for scoping and cleaning prior to initial field connection

EDGE™ MTP® PRO Jumper, 12F, Bend-Improved single-mode (OS2), MTP PRO (pinned) to MTP PRO (pinned), Plenum, TIA-568-Type-A, 10 ft

12-Fiber MTP® PRO Jumper 12F, Bend-Improved single-mode (OS2), 10 ft

CORNING

Specifications

General Specifications

Flame Rating	NFPA 262 (for plenum, riser and general building applications)
Fiber Category	Bend-improved SM (OS2)
Cable Assembly Type	EDGE™ Jumper
Environment	Indoor
Application	Data Center
Cable Type	Interconnect
Assembly Insertion Loss	≤ 0.7 dB
Connector Assembly Type	MTP to MTP

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Environmental Conditions

Temperature Range, Installation	0 °C to 50 °C (32 °F to 122 °F)
Temperature Range, Operation	-10 °C to 60 °C (14 °F to 140 °F)

Design

Fiber Count	12
Polarity	TIA-568 Type-A
Fiber Type	Single-mode

Mechanical Specifications

Nominal Outer Diameter	2 mm (0.08 in)
Max. Tensile Strength for Installation	220 N (49.46 lbf)
Min. Bend Radius Installation	30 mm (1.18 in)

12-Fiber MTP® PRO Jumper 12F, Bend-Improved single-mode (OS2), 10 ft

CORNING

Mechanical Specifications

Min. Bend Radius Operation	10 mm (0.39 in)
Weight	3.5 kg/km (2.35 lb/1000 ft)

Optical Characteristics

Fiber Code	Z
Performance Option Code	01
Fiber Category	OS2
Fiber Type	Single-mode (OS2) / 250 µm
Fiber Name	Bend-Improved Single-mode (OS2)
Maximum Attenuation	0.4 dB/km / 0.4 dB/km / 0.3 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Compliance	ITU-T G.652.D and ITU-T G.657.A1

Specifications - Connector A

Polish	APC
Insertion Loss, Max.	0.35 dB
Boot Color	Black
Connector Type	MTP® PRO (pinned)
Ferrule Material	Composite
Boot Type	Simplex
Reflectance	< -65 dB

Specifications - Connector B

Polish	APC
Insertion Loss, Max.	0.35 dB
Boot Color	Black
Connector Type	MTP® PRO (pinned)
Ferrule Material	Composite

12-Fiber MTP® PRO Jumper 12F, Bend-Improved single-mode (OS2), 10 ft

CORNING

Specifications - Connector B

Boot Type	Simplex
Reflectance	< -65 dB

Dimensions

Length	10 ft
Cable Weight	3.5 kg/km (2.35 lb/1000 ft)

Ordering Information

Product Number	J898912GE8-NA010F
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.