

Wall-Mountable Connector Housing (WCH) Holds 6 CCH connector panels/cassettes

CORNING

Part Number: WCH-06P

Corning wall-mountable connector housing (WCH) product family offers enhanced innovative features that make installation and troubleshooting of fiber optic connectivity faster, easier and more cost-effective. From fiber and cable routing and strain-relief to port labeling and termination, these housings reduce the risk of error that can disrupt networks. The WCH housing provides interconnect or cross-connect capabilities between the outside plant, riser or distribution cables and the opto-electronics. With the WCH-02P (two panels, cassettes or modules), WCH-04P (four panels, cassettes or modules), and WCH-06P (six panels, cassettes or modules) capacity, the rugged metal housings can be wall mounted in main cross-connections, telecommunication rooms or other areas where space is a premium. Units accept standard closet connector housing (CCH) cassettes, connector panels and modules for a variety of connectivity options. The WCH product family features a clear, transparent jumper side door for easy visibility during installation and testing, easy-to-use recessed mounting holes with mounting screws, documentation labels, removable strain-relief brackets, routing clips and guides, improved latches, as well as a preinstalled bubble level for simple and accurate installation. All housings also have field-installable lock kits available for both cable entry and jumper side doors.

Features and Benefits

Interconnect and cross-connect capabilities

Ideal for field splicing and connectorization

Accepts CCH cassettes, panels and modules

Variety of preterminated and field-installable capabilities

Lockable, transparent jumper side door

Visibility and ease of access for installation, testing and troubleshooting

Removable strain-relief bracket

Flexibility for installation and moves, adds and changes (MACs)

Segregated cable and fiber slack routing

Fiber protection



Wall-Mountable Closet Housing (WCH), holds 6 CCH connector panels/cassettes

Wall-Mountable Connector Housing (WCH) Holds 6 CCH connector panels/cassettes

CORNING

Specifications

General Specifications

Product Type	Housings
Mounting Type	Wall-Mountable
Application	Enterprise Networks

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Lockable	Yes
Maximum Fiber Capacity	144
Housing Type	WCH
Splice Tray / Splice Cassette Options	Up to 6 CCH cassettes
Lock Position	Provider door and jumper door

Connector Specs

Housing Color	Black
---------------	-------

Dimensions

Height	357.6 mm
Width	410.5 mm
Depth	164.3 mm

Ordering Information

Product Number	WCH-06P
----------------	---------

Wall-Mountable Connector Housing (WCH) Holds 6 CCH connector panels/cassettes

CORNING

Ordering Information

Package Contents	Housing; installation guide; 6 blank panels; 6 panel ID labels; hardware kit; internal strain-relief bracket; intermediate strain-relief bracket; 4 x 4-in tie wraps; 4 x 8-in tie wraps; dust brushes; 4 mounting screws; bubble level
Shipping Weight	4.58 kg
Shipping Height	510 mm
Shipping Width	448 mm
Shipping Depth	248 mm
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.