

EDGE™ Housing 4 rack units, Gray, holds up to 48 EDGE modules or panels

CORNING


Part Number:
EDGE-04U

EDGE™ housings are high-density, preterminated fibre optic hardware solutions. They offer industry-leading connector density and easy finger/toolless access to enable faster moves, adds, and changes (MACs). The units can be configured to accommodate 96, 144, 288, or 576 fibers.

EDGE housings can be rack- or cabinet-mounted and are ideal for data centers, local area network (LAN) and storage area network (SAN) applications, as well as enterprise networks.



EDGE™ Housing, 4 rack units, holds up to 48 EDGE modules or panels



EDGE™ Housing, 4 rack units, holds up to 48 EDGE modules or panels

EDGE™ Housing 4 rack units, Gray, holds up to 48 EDGE modules or panels



EDGE™ Housing, 4 rack units, holds up to 48 EDGE modules or panels

Specifications

General Specifications	
Product Type	Housings
Access Type	Front and rear access slidable
Mounting Type	Rack-mount, Cabinet-mount
Application	Data Center, Enterprise Networks
Brand	EDGE

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Design	
Lockable	Yes
Number of Modules	48
Cable entry type	Side brush entry

EDGE™ Housing 4 rack units, Gray, holds up to 48 EDGE modules or panels

CORNING

Design

Number of Panels/Cassettes per Housing	48
Cable Entry Direction	Rear
Housing Type	EDGE
Color	Silver
Panel or Cassette Type	EDGE
Panel or Module Type	EDGE
Fiber Capacity	576
Lock Position	Rear

Design - Adapter

Housing Color	Silver
---------------	--------

Dimensions

Height	177 mm
Width	432 mm
Depth	561 mm
Weight	14.5 kg

Ordering Information

Product Number	EDGE-04U
Module Capacity	48
Height Unit	4 U
Trunk Capacity	48 (size 1 or 2, double stack cradle)
Package Contents	EDGE™ Housing 4U; Quick Start Guide, #12-24 and #10-32 mounting screws, Cage Nut Mounting Kit, Velcro Strap, Fiber Optic Warning Label
Shipping Weight	16.8 kg
Shipping Height	305 mm

EDGE™ Housing 4 rack units, Gray, holds up to 48
EDGE modules or panels



Ordering Information	
Shipping Width	565 mm
Shipping Depth	660 mm
Units per Delivery	1/1



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.