

# Centrix™ Front Access Cabinet Single Cabinet, H1200xW900xD300, left cable entry, walls, metal doors, no bottom channel, assembled



**Part Number:**  
**CTX-CAB-F1209PMLAN**

Centrix™ Front Access Cabinet, Single Cabinet, H1200xW900xD300, left cable entry, walls, metal doors, no bottom channel, assembled.

The Centrix™ single cabinet provides space for up to 60 Centrix cassettes with a maximum capacity of 2160 LC or 1440 SC single fiber ports. All functions are accessible from the front of the cabinet. The patch cord management enables in-cabinet Cross-Connects with a single patch chord length of 2.5 m. Feeder cables can enter the cabinet from top and bottom. The cabinet comes assembled for fast deployment.

## Features and Benefits

All front access

---

20 rack units

---

Supports 2.160 LC or 1.440 SC ports per cabinet on 0.27 m<sup>2</sup>

---

Integrated patch cord management

---

Single 2.5 m patch cord for in-frame Cross-Connect

---

Quick installation feature for Centrix housings

---

Assembled for fast deployment

---

3 cable strain relief plates included

---

5 numbered cable routing hubs included

---

Extendable to dual- or quad cabinet Cross-Connect with a single patch cord length (2.5 m)

---

All front access

---

40 rack units

---

Supports 4.320 LC or 2.880 SC ports per cabinet on 0.27 m<sup>2</sup>

---

Integrated patch cord management

# Centrix™ Front Access Cabinet Single Cabinet, H1200xW900xD300, left cable entry, walls, metal doors, no bottom channel, assembled



## Specifications

|               |         |
|---------------|---------|
| ◆◆◆◆          |         |
| ◆◆◆◆          | Centrix |
| ◆◆◆◆          | ◆◆◆◆    |
| ◆◆◆◆          | ◆◆◆◆    |
| ◆◆◆◆          | ◆       |
| Preterminated | ◆       |

|      |                         |
|------|-------------------------|
| ◆◆   |                         |
| RoHS | ◆◆◆◆◆◆◆◆RoHS 2011/65/EU |

|          |   |
|----------|---|
| ◆◆       |   |
| ◆◆◆◆◆◆◆◆ | ◆ |



|        |         |
|--------|---------|
| ◆◆     |         |
| ◆◆     | 1400 mm |
| ◆◆     | 900 mm  |
| ◆◆     | 300 mm  |
| Weight | 45 kg   |

|                 |                    |
|-----------------|--------------------|
| ◆◆◆◆            |                    |
| ◆◆◆◆            | CTX-CAB-F1209PMLAN |
| ◆◆◆◆            | 20 U               |
| Shipping Weight | 65 kg              |
| ◆◆◆◆◆◆◆◆◆◆      | 1/1                |

# Centrix™ Front Access Cabinet Single Cabinet, H1200xW900xD300, left cable entry, walls, metal doors, no bottom channel, assembled

CORNING



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 •    
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/emea/trademarks](http://www.corning.com/opcomm/emea/trademarks). Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.