

Centrix™ Front Access Cabinet Single Cabinet, H1800xW900xD300, left cable entry, no walls, no doors, bottom channel, flat pack



Part Number:
CTX-CAB-F1809NNLNB

Centrix™ Front Access Cabinet, Single Cabinet, H1800xW900xD300, left cable entry, no walls, no doors, bottom channel, flat pack

The Centrix™ single cabinet provides space for up to 96 Centrix cassettes with a maximum capacity of 3456 LC or 2304 SC single fiber ports. All functions are accessible from the front of the cabinet. The patch cord management enables in-cabinet Cross-Connects with a single patch chord length of 3.5 m. Feeder cables can enter the cabinet from top and bottom. The bottom channel function provides for easy routing of patch cords accross cabinets in a row. The cabinet comes in flat packs for easy transport.

Features and Benefits

All front access

32 rack units

Supports 3.456 LC or 2.304 SC ports per cabinet on 0.27 m²

Integrated patch cord management

Single 3.5 m patch cord for in-frame Cross-Connect

Quick installation feature for Centrix housings

Flat pack for easy transport

4 cable strain relief plates included

8 numbered cable routing hubs included

Extendable to dual- or quad cabinet Cross-Connect with a single patch cord length (3.5 m)

All front access

40 rack units

Supports 4.320 LC or 2.880 SC ports per cabinet on 0.27 m²

Centrix™ Front Access Cabinet Single Cabinet, H1800xW900xD300, left cable entry, no walls, no doors, bottom channel, flat pack



Specifications

◆◆◆◆	
◆◆◆◆	Centrix
◆◆◆◆	◆◆◆◆
◆◆◆◆	◆◆◆◆
◆◆◆◆	◆
Preterminated	◆

◆◆	
RoHS	◆◆◆◆◆◆◆◆RoHS 2011/65/EU

◆◆	
◆◆◆◆◆◆◆◆	◆



◆◆	
◆◆	2000 mm
◆◆	900 mm
◆◆	300 mm
Weight	50 kg

◆◆◆◆	
◆◆◆◆	CTX-CAB-F1809NNLNB
◆◆◆◆	32 U
Shipping Weight	90 kg
◆◆◆◆◆◆◆◆◆◆	1/1

Centrix™ Front Access Cabinet Single Cabinet, H1800xW900xD300, left cable entry, no walls, no doors, bottom channel, flat pack

CORNING



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 •  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.