

Building Access Terminal (BAT) Size XL, grey, EMKA lock, 16 cable strain reliefs




Part Number:
BAT-XGE-ST001

The Building Access Terminal (BAT) is available in sizes XS (Small Floor Terminal), S, M, L, XL to address different capacity requirements. It is offered in white or grey color and lockable with a Screw- or EMKA-Lock.

Features and Benefits

- Can be locked with lock or screw (M4)
- Plastic FRNC
- White or grey colour
- Cover completely removable
- Clip to store documents
- Side walls shaped to ensure maximum freedom of accessibility
- Strain-relief for cables up to 12mm diameter
- Modular configurable and extendable
- Integrated channel to reduce installation time



Building Access Terminal (BAT), Size XL, grey, EMKA lock, 16 cable strain reliefs



Building Access Terminal (BAT), Size XL, grey, EMKA lock, 16 cable strain reliefs

Building Access Terminal (BAT) Size XL, grey, EMKA lock, 16 cable strain reliefs

CORNING



Specifications

General Specifications

Suitable for	250 µm and 900 µm bare fibres
Product type	Housings
Environment	Indoor/Outdoor
Mounting Type	Wall-mount

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Environmental Conditions

Temperature range, installation	-33 °C to 70 °C
Temperature range, operation	-33 °C to 70 °C
Temperature range, storage	-25 °C to 70 °C

Building Access Terminal (BAT) Size XL, grey, EMKA lock, 16 cable strain reliefs

CORNING

Design	
Lockable	Yes
Splice tray type	Own
Housing material	Composite and PC ABS
Additional cable number reached w/accessories	64
Max. cable number in basic unit w/accessories	20
Number of blank modules	44
Cable entry type	Grommeted slot
Number of splice trays	3
Adapter type front	LC duplex
Colour	Grey
Pigtail type	Individual with natural primary coating and yellow secondary coating
Number of adapters	20
Lock Position	Front
Lock Type	Screw cap or EMKA lock

Design - Adapter	
Adapter housing colour	Green
Keyed adapter	Yes
Shuttered adapter	No

Optical Specification - Hardware	
Pigtail insertion loss	0.35 dB

Specifications - Connector A	
Connector type	LC duplex

Building Access Terminal (BAT) Size XL, grey, EMKA lock, 16 cable strain reliefs

CORNING

Dimensions

Height	390 mm
Width	450 mm
Depth	88 mm
Weight	2.5 kg

Ordering Information

Product Number	BAT-XGE-ST001
Package contents	4 screws and 4 dowels
Shipping weight	2.5 kg
Shipping Height	100 mm
Shipping Width	500 mm
Shipping Depth	500 mm
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.