

Pretium® Connector Housing (PCH) 1 rack unit, holds 3 CCHE Plug & Play™ Reduced-Depth Modules



**Part Number:
PCH-M3-01U**

The rack-mount Pretium® connector housings (PCH) are available in 1U, 2U and 4U sizes and mount in 19-in racks or cabinets. Combined with the modules, panels, harnesses, trunks and patch cords, they provide a tip-to-tip solution for your fiber optic network.

Features and Benefits

Compatible with Plug & Play™ Systems modules

Designed to support Plug & Play Systems applications

Splice in the housing

Saves rack space and the cost of the second housing

Removable top (1U, 2U)


Maximizes ease of access

Transparent front door (04U and 02U)

Permits viewing while protecting installed patch cords

Large removable fiber guides in front

Effectively manage high patch cord densities



Pretium® 3-Module Housing, 1 rack unit, holds three CCHE Plug & Play™ reduced-depth modules

Pretium® Connector Housing (PCH) 1 rack unit, holds 3 CCHE Plug & Play™ Reduced-Depth Modules



Specifications

General Specifications	
Product type	Rack-Mountable Hardware
Mounting Type	Rack-mount
Application	Data Centre, Enterprise Networks

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
UL-Listed	United States and Canadian safety standards

Design	
Housing type	PCH
Number of panels per housing	3
Panel or module type	CCH
Fibre Capacity	Up to 36 fibres installing SC/ST@/SC Duplex connectors, or up to 72 installing LC Duplex or MTRJ connectors

Design - Adapter	
Adapter housing colour	Grey

Dimensions	
Height	445 mm

Ordering Information	
Product Number	PCH-M3-01U
Height Unit	1 U
Package contents	Housing; installation guide; 3 blank panels; unit ID label; 4 #10-32 x 50 screws; 4 #12-24 x 50 screws

Pretium® Connector Housing (PCH) 1 rack unit, holds 3 CCHE Plug & Play™ Reduced-Depth Modules



Ordering Information	
Shipping weight	1.75 kg
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.