

EDGE™ Housing 1 rack unit, Gray, holds up to 8 EDGE modules or panels

CORNING

Part Number:
EDGE-01U

EDGE™ housings are high-density, preterminated fibre optic hardware solutions. They offer industry-leading connector density and easy finger/toolless access to enable faster moves, adds, and changes (MACs). The units can be configured to accommodate 96, 144, 288, or 576 fibers.

EDGE housings can be rack- or cabinet-mounted and are ideal for data centers, local area network (LAN) and storage area network (SAN) applications, as well as enterprise networks.



EDGE™ Housing 1 rack unit, Gray, holds up to 8 EDGE modules or panels

CORNING

Specifications

General Specifications

Product Type	Housings
Access Type	Front and rear access slidable
Mounting Type	Rack-mount, Cabinet-mount
Application	Data Center, Enterprise Networks
Brand	EDGE

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Lockable	Yes
Number of Modules	8
Cable entry type	Side brush entry
Number of Panels/Cassettes per Housing	8
Cable Entry Direction	Rear
Housing Type	EDGE
Color	Silver
Panel or Cassette Type	EDGE
Panel or Module Type	EDGE
Fiber Capacity	96
Lock Position	Rear

Design - Adapter

Housing Color	Silver
---------------	--------

EDGE™ Housing 1 rack unit, Gray, holds up to 8 EDGE modules or panels

CORNING

Dimensions

Height	44 mm
Depth	561 mm
Weight	5.4 kg

Ordering Information

Product Number	EDGE-01U
Module Capacity	8
Height Unit	1 U
Trunk Capacity	12 (size 1 or 2)
Package Contents	EDGE™ Housing 1U; Quick Start Guide, #12-24 and #10-32 mounting screws, Cage Nut Mounting Kit, Velcro Strap, Fiber Optic Warning Label
Shipping Weight	7.7 kg
Shipping Height	171 mm
Shipping Width	565 mm
Shipping Depth	657 mm
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.