

EDGE™ Housing 1 rack unit, gray, holds up to 12 EDGE modules or panels

CORNING

Part Number:
EDGE-01U-SP

EDGE™ housings are high-density, preterminated fibre optic hardware solutions. They offer industry-leading connector density and easy finger/toolless access to enable faster moves, adds, and changes (MACs). The units can be configured to accommodate 96, 144, 288, or 576 fibers.

EDGE housings can be rack- or cabinet-mounted and are ideal for data centers, local area network (LAN) and storage area network (SAN) applications, as well as enterprise networks.



EDGE™ Housing, 1 rack unit, gray, holds up to 12 EDGE modules or panels



EDGE™ Housing, 1 rack unit, gray, holds up to 12 EDGE modules or panels

EDGE™ Housing 1 rack unit, gray, holds up to 12 EDGE modules or panels

CORNING

Specifications

General Specifications

Product Type	Housings
Access Type	Front and rear access slidable
Mounting Type	Rack-mount, Cabinet-mount
Application	Data Center, Enterprise Networks

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Lockable	Yes
Number of Modules	12
Cable entry type	Side brush entry
Number of Panels/Cassettes per Housing	12
Cable Entry Direction	Rear
Housing Type	EDGE
Color	Silver
Panel or Cassette Type	EDGE
Panel or Module Type	EDGE
Fiber Capacity	144
Lock Position	Rear

Design - Adapter

Housing Color	Silver
---------------	--------

EDGE™ Housing 1 rack unit, gray, holds up to 12 EDGE modules or panels

CORNING

Dimensions

Height	44 mm (1.73 in)
Width	432 mm (17.01 in)
Depth	561 mm (22.09 in)
Weight	6.4 kg

Ordering Information

Product Number	EDGE-01U-SP
Module Capacity	12
Height Unit	1 U
Trunk Capacity	12 (size 1 or 2)
Package Contents	EDGE™ Housing 1U; Quick Start Guide, #12-24 and #10-32 mounting screws, Cage Nut Mounting Kit, Velcro Strap, Fiber Optic Warning Label
Shipping Weight	8.2 kg
Shipping Height	171 mm (6.73 in)
Shipping Width	565 mm (22.24 in)
Shipping Depth	646 mm (25.43 in)
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.