Wall-Mountable Connector Housing (WCH) Holds 2 CCH connector panels/cassettes

Part Number:
WCH-02P

Corning wall-mountable connector housing (WCH) product family offers enhanced innovative features that make installation and troubleshooting of fiber optic connectivity faster, easier and more cost-effective. From fiber and cable routing and strain-relief to port labeling and termination, these housings reduce the risk of error that can disrupt networks. The WCH housing provides interconnect or cross-connect capabilities between the outside plant, riser or distribution cables and the opto-electronics. With the WCH-02P (two panels, cassettes or modules), WCH-04P (four panels, cassettes or modules), and WCH-06P (six panels, cassettes or modules) capacity, the rugged metal housings can be wall mounted in main cross-connects, telecommunication rooms or other areas where space is a premium. Units accept standard closet connector housing (CCH) cassettes, connector panels and modules for a variety of connectivity options. The WCH product family features a clear, transparent jumper side door for easy visibility during installation and testing, easy-to-use recessed mounting holes with mounting screws, documentation labels, removable strain-relief brackets, routing clips and guides, improved latches, as well as a preinstalled bubble level for simple and accurate installation. All housings also have field-installable lock kits available for both cable entry and jumper side doors.



Wall-Mountable Closet Housing (WCH), holds 2 CCH connector panels/ cassettes

Features and Benefits

Interconnect and cross-connect capabilities
Ideal for field splicing and connectorization

Accepts CCH cassettes, panels and modules
Variety of preterminated and field-installable capabilities

Lockable, transparent jumper side door
Visibility and ease of access for installation, testing and troubleshooting

Removable strain-relief bracket
Flexibility for installation and moves, adds and changes (MACs)

Segregated cable and fiber slack routing
Fiber protection

Wall-Mountable Connector Housing (WCH) Holds 2 CCH connector panels/cassettes

Specifications

General Specifications	
Product Type	Housings
Mounting Type	Wall-Mountable
Application	Enterprise Networks

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Design	
Lockable	Yes
Maximum Fiber Capacity	48
Housing Type	WCH
Splice Tray / Splice Cassette Options	Up to 2 CCH cassettes
Lock Position	Provider door and jumper door

Connector Specs	
Housing Color	Black

Dimensions	
Height	192 mm (7.56 in)
Width	410.5 mm (16.16 in)
Depth	113 mm (4.45 in)

Ordering Information	
Product Number	WCH-02P

Wall-Mountable Connector Housing (WCH) Holds 2 CCH connector panels/cassettes

CORNING

Ordering Information	
Package Contents	Housing; installation guide; 2 blank panels; 2 panel ID labels; hardware kit; internal strain-relief bracket; intermediate strain-relief bracket; 4 x 4-in tie wraps; 4 x 8-in tie wraps; dust brushes; 4 mounting screws; bubble level
Shipping Weight	3.22 kg
Shipping Height	510 mm (20.08 in)
Shipping Width	283 mm (11.14 in)
Shipping Depth	216 mm (8.5 in)
Units per Delivery	1/1

RoHS COMPLIANT

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.