

Everon® Copper Datacom V250 Unshielded VOCK6UHBL8, V250UBL, RJ45 Vol, Cat6, Bag/8, Blue

CORNING

Part Number:
XF500006309

Our Cat.6 copper interconnect products work together to provide an easy-to-use solution for deploying high-speed connections throughout a building. The RJ45 jack is a key component in this system. These RJ45 jacks have been certified by an independent test laboratory to hardware certification. Each jack component is able to terminate to any certified Cat.6 TIA, ISO/IEC and EN standards for hardware performance, confirmed by independent laboratory certifications. The jack's unique three cable entry points help make installation simple. The traditional one-click design enables an easy, tool-less termination on Cat. 6 unshielded twisted pair cables, meeting industry performance standards.

Features and Benefits

Tool-less jack

Easy and quick to install - reliable connection
The conductors are wired in a single operation

Three cable entry points

Less cable bending required - better compliance with minimum bend radius

No untwisting of pairs before termination

Minimized stripping length - limited pair untwist - pairs kept together, no wire guide required

Accepts solid and stranded conductors

Enables "jack-to-plug" cables to be manufactured using stranded conductors

Accepts solid and stranded conductors

Enables "jack-to-plug" cables to be manufactured using stranded conductors

Hardware Performance

Can be mixed and matched with other Hardware certified copper cable and patchcords

Tested and approved for Power over Ethernet applications (PoE/PoE+/4PPoE) according to IEEE 802.3af, IEEE 802.3at and IEEE 802.3bt up to 90W



Everon® Copper Datacom V250 Unshielded VOCK6UHBL8, V250UBL, RJ45 Vol, Cat6, Bag/8, Blue



Specifications

General Specifications

Category	6
----------	---

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	ISO/ IEC 11801 Edition 2. Arm 1-2, EN 50173-1 : 2011,ANSI/ TIA/ EIA-568-C.2-2009, ISO/IEC 60603-7-51:2010
Design and Test Criteria	IEEE 802.3 1GBASE-T, IEEE 802.3at

Design

Jack Type	RJ45 - 8/8
Housing Material	Plastic
Color	Blue
Insulation diameter max.	1.6 mm
Conductor	24 - 22 AWG
Number of Stranded Wires	7

Mechanical Specifications

Contact surface	Gold, 1.27 μ m
Reproducibility	Several times reusable
Solid Wire Diameter	5 mm to 65 mm

Electrical Specifications

Lead Through Resistance	< 200 m Ω
Insulation Resistance	> 500 M Ω
Voltage Rating (Maximum)	<75

Everon® Copper Datacom V250 Unshielded VOCK6UHBL8, V250UBL, RJ45 Vol, Cat6, Bag/8, Blue



Dimensions	
Height	23 mm
Width	18 mm
Depth	34 mm

Ordering Information	
Product Number	XF500006309
Packaging Method	Bag of 8 / 1 Box
Shipping Weight	135 kg
Units per Delivery	96/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.