

Centrix™ loaded housing 2U, 6 Cassettes each with 24 SC UPC adapters and SM pigtails, 250 μm standard SM pigtails, total of 144 F



Part Number:
CX2E4P24-3C-2RH000

A Centrix™ System 4U housing holds 12 cassettes. Housings can be ordered with cassettes for on-frame splicing. At the foundation of the Centrix System is a single, modular cassette that can be tailored to include a variety of optical devices (splitter, WDM, etc). The modular cassette provides flexibility and functionality within a single frame without sacrificing density. Each cassette contains up to either 24 SC or 36 LC connector adapters. Easy port access is possible due to a sliding cassette with drop-down handle.



Centrix™ loaded housing 2U, 6 Cassettes each with 24 SC UPC adapters and SM pigtails, 250 μm standard SM pigtails, total of 144 F



Specifications

General Specifications

Product Type	Housings
--------------	----------

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Environmental Conditions

Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
------------------------------	-------------------------------------

Design

Pigtail Type	900 μm
--------------	--------

Specifications - Connector B

Connector Type	SC
----------------	----

Polish	UPC
--------	-----

Dimensions

Height	889 cm
--------	--------

Width	52.1 cm
-------	---------

Depth	305 cm
-------	--------

Weight	10.4 kg
--------	---------

Ordering Information

Product Number	CX2E4P24-3C-2RH000
----------------	--------------------

Height Unit	2 U
-------------	-----

Centrix™ loaded housing 2U, 6 Cassettes each with 24 SC UPC adapters and SM pigtails, 250 μm standard SM pigtails, total of 144 F



Ordering Information	
Shipping Weight	11.8 kg
Shipping Height	282 cm
Shipping Width	55.9 cm
Shipping Depth	422 cm
Units per Delivery	1/1



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.