

MiniXtend® HD Cable with Binderless* FastAccess® Technology 12 F (1x12), G.657.A1 190

CORNING

Part Number:
012ZM4-T4E49A20

Corning® MiniXtend® HD Cables with Binderless* FastAccess® Technology are high-density micro cables that are up to 60 percent smaller and up to 70 percent lighter than standard loose tube cables and up to 20 percent smaller than standard micro cables.

The innovative Binderless FastAccess Technology improves cable handling and reduces access time up to 70 percent while lowering risk of cable and fiber damage. MiniXtend HD cables have an SZ-stranded loose tube construction and provide high fiber counts in limited duct space in long-haul, metro and access networks.

With a low-friction PE sheath, MiniXtend HD cables are optimized for blowing into microducts. Both the buffer tubes and the fibers contained within are color-coded for quick and easy identification.

MiniXtend HD cables feature Corning® SMF-28® Ultra 200 single-mode fiber (ITU-T G.652.D and ITU-T G.657. A1): the industry's first 200 micron fiber with a 9.2 micron mode-field diameter (MFD).

Features and Benefits

Binderless FastAccess® Technology

Innovative cable design that reduces cable access time up to 70 percent and lowers the risk of inadvertent fiber damage

Reduced outer cable diameter

High fiber density in microduct systems

Compact and light

CapEx-optimized installations and upgrades

Fully dielectric

No grounding required

Color-coded tubes and fibers

Easy identification of tubes and fibers

MiniXtend® HD Cable with Binderless* FastAccess® Technology 12 F (1x12), G.657.A1 190

CORNING

Specifications

General Specifications

Installation Methods	Microduct
Cable Type	Stranded Loose Tube
Environment	Outdoor
Product Type	Dielectric
Fiber Category	G.652.D/G.657.A1
Cable geometry	Round

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Environmental Conditions

Temperature Range, Installation	-5 °C to 50 °C (23 °F to 122 °F)
Temperature Range, Operation	-20 °C to 70 °C (-4 °F to 158 °F)
Temperature Range, Storage	-30 °C to 70 °C (-22 °F to 158 °F)

Cable Design

Cable Marking	M#H#S#CORNING#YEAR MINIXTEND®HD FAB CABLE 1x12 G.657.A1 190 LT1.1#ID Number
Central Element	Dielectric
Fiber Count	12
Buffer Tube Color Coding, Layer 1	Blue
Outer Jacket Color	Black
Outer Jacket Material	Polyethylene (PE)
Outer Jacket Nominal Thickness	0.5 mm
Buffer Tube Diameter	1.13 mm
Number of Active Tubes	1

MiniXtend® HD Cable with Binderless* FastAccess® Technology 12 F (1x12), G.657.A1 190

CORNING

Cable Design

Number of Tube Positions	6
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Fibers per Tube	12
Color Code Standards	Telcordia

Mechanical Specifications

Crush Resistance (reversible), Outdoor Cable	500 N/10 cm
Max. Tensile Strength, Short-Term	350 N
Nominal Outer Diameter	4.5 mm
Min. Bend Diameter Installation	180 mm
Min. Bend Diameter Operation	136 mm
Min. Duct Size Diameter	6 mm
Optimal Duct Size	8 mm

Dimensions

Cable Weight	14.7 kg/km
Max. cable length per reel/drum	6096 m



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.