

Centrix™ Front Access Cabinet Dual Cabinet, H2200xW1800xD300, side-by-side, centered patch cord management, walls, doors, acrylic glass window, bottom channel, assembled



Part Number:
CTX-CAB2F2218PGBAB

Centrix™ Front Access Cabinet, Dual Cabinet, H2200xW1800xD300, side-by-side, centered patch cord management, walls, doors, acrylic glass window, bottom channel, assembled.

The Centrix™ dual cabinet (side-by-side) provides space for up to 240 Centrix cassettes with a maximum capacity of 8640 LC or 5760 SC single fiber ports. All functions are accessible from the front of the cabinet. The patch cord management enables in-cabinet Cross-Connects with a single patch chord length of 4 m. Feeder cables can enter the cabinet from top and bottom. The bottom channel function provides for easy routing of patch cords accross cabinets in a row. The cabinet comes assembled for fast deployment.

Features and Benefits

Side-by-Side configuration

All front access

80 rack units

Supports 8.640 LC or 5.760 SC ports per cabinet on 0,54 m²

Integrated patch cord management

Single 4 m patch cord for in-frame Cross-Connect

Quick installation feature for Centrix housings

Assembled for fast deployment

10 cable strain relief plates included

20 numbered cable routing hubs included

Extendable to quad cabinet Cross-Connect with a single patch cord length (4 m)

All front access

40 rack units



Centrix™ Front Access Cabinet Dual Cabinet, H2200xW1800xD300, side-by-side, centered patch cord management, walls, doors, acrylic glass window, bottom channel, assembled



Centrix™ Front Access Cabinet, Dual Cabinet, H2200xW1800xD300, side-by-side, centered patch cord management, walls, doors, acrylic glass window, bottom channel, assembled

Specifications

General Specifications	
Product Type	Centrix™
Access Type	Front access
Mounting Type	Cabinet-mount
Splice option	Yes
Preterminated	Yes

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Design	
Cable Entry Direction	Side

Centrix™ Front Access Cabinet Dual Cabinet, H2200xW1800xD300, side-by-side, centered patch cord management, walls, doors, acrylic glass window, bottom channel, assembled

CORNING

Dimensions

Height	2400 mm
Width	1800 mm
Depth	300 mm
Weight	180 kg

Ordering Information

Product Number	CTX-CAB2F2218PGBAB
Height Unit	80 U
Shipping Weight	215 kg
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.