

EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Straight-through Polarity (TIA)



Part Number:
ETM-5B-G-S

EDGE Tap module for traditional LC duplex systems enables the customer to manage the monitoring access points via the patch cord infrastructure zone at the front of the cabinets. The Edge Tap Module enables passive optical tapping of the network while reducing downtime and link loss, and increasing rack space utilization and density.


Features and Benefits

Designed for Duplex based infrastructure solutions


Utilizes advanced splitter technology

Maintains equal modal power distribution, reducing insertion loss for increased link reach

EDGE Solutions-based footprint



EDGE™ Solutions Tap Module, Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Straight-through Polarity (TIA Type A)



EDGE™ Solutions Tap Module, Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Straight-through Polarity (TIA Type A)

EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Straight-through Polarity (TIA



Specifications

General Specifications

Product Type	Modules
Fiber Category	Single-mode (OS2)
Mounting Type	Rack-mount
Application	Data Center

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Adapter Type Back	MTP®
Adapter Color Back	Black / Red
Adapter Color Front	Blue
Adapter Type Front	Shuttered LC
Housing Type	Modules
Number of Ports	12
Number of Adapters per Panel	6

Cable Design

Polarity	Straight-Through, TIA-568 Type-A
----------	----------------------------------

Specifications - Connector A

Connector Type	LC duplex
Ferrule Material	Ceramic

EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Straight-through Polarity (TIA



Specifications - Connector B	
Connector Type	MTP® (pinned)
Ferrule Material	Ceramic

Dimensions	
Weight	16 kg

Ordering Information	
Product Number	ETM-5B-G-S
Units per Delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.