

Centrix™ Splice Cassette 8x LC Duplex/APC adapters and 16x LC/APC single fiber pigtails (OS2)

CORNING

Part Number:
CTXCPP16-B3-2RH000

The Centrix™ splice cassette provides 24 LC APC single fiber ports. The cassette is loaded with 12 LC Duplex APC adapters, colored LC single fiber pigtails and accepts crimp or heat-shrink splice protectors. A drop handle provide fiber port protection, patch cord organization and labeling on front and top of the cassette. The cassette is slidable in Centrix housings and is secured with a latch mechanism. The jumper guide direction is to the left side of the cassette but can simply be changed with accessories to the right. The transparent and captive top and bottom cover enable easy handling and visual inspection or trouble shooting. The multiple tube entry points on the cassette provide flexible loading of buffer tubes and bare fibers in the cassette.

Features and Benefits

Easy port access and identification

Easy port access and identification

Integrated patch cord guide supports patch management

Front and top labeling for easy identification

Captive covers on both sides of the cassette

Transparent covers enable trouble shooting

Bare fiber and tube slack storage up to 2m by design

Multiple tube entry from the rear or both sides on the cassette

Centrix™ Splice Cassette 8x LC Duplex/APC adapters and 16x LC/APC single fiber pigtails (OS2)



Specifications

□ □ □ □	
□ □ □ □	Centrix
□ □ □ □	□ □ (OS2)
□ □ □ □	250 μm
□ □	
RoHS	□ □ □ □ □ □ □ □ RoHS 2011/65/EU
□ □ □ □ □	
□ □ □ □ □ □ □ □	-40 °C - 70 °C (-40 °F - 158 °F)
□ □	
□ □ □ □	900 μm
□ □ □	16
□ □ □ □ □ □ - □ □	
□ □ □ □	≤ 0.25 dB
Min. Reflectance	-65 dB
Connector Specs	
□ □	APC
□ □ □ □ □ □	LC
□ □	
Weight	0.5 kg

Centrix™ Splice Cassette 8x LC Duplex/APC adapters and 16x LC/APC single fiber pigtails (OS2)



◆◆◆◆	
◆◆◆◆	CTXCPP16-B3-2RH000
Shipping Weight	0.85 kg
◆◆◆◆◆◆◆◆	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • ◆◆
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.