

K7 Splice Cassette 2 Slots, Uni Zone-24+24

The CORNING logo is displayed in white, uppercase letters within a solid blue rectangular box.

Part Number:
N541271A

The type of splice technology used (fusion or mechanical) and whether planar light circuit (PLC) splitters are required will help determine which BPEO splice tray should be selected.

- Compact trays are 5 mm in height and occupy one slot in the fiber organizer.
- Standard trays are 10 mm in height and occupy two slots.
- All BPEO splice trays accept heat-shrink fusion splice protectors of 2.4 mm x 45 mm or 2.4 mm x 60 mm (after shrinkage). For example, Fiber Closure BPEO size 1 is equipped with a 12-slot fiber organizer. If using a 5 mm tray for 12 fusion splices, the total capacity of the closure will be 144 splices.

K7 Splice Cassette 2 Slots, Uni Zone-24+24



Specifications

General Specifications

Brand	BPEO
Product Type	Splice Trays

Standards

Fiber Standards	G.652 / G.657
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Design

Splice Tray Type	K7 Splice Tray
Number of Splice Trays	1
Color	Light basic, RAL 7035
Splice Protectors Type	Heat Shrink
Splice Tray Capacity Single Fiber	48
Number of Splice Protectors	48

Dimensions

Height	10 mm
--------	-------

Ordering Information

Product Number	N541271A
Packaging Method	Box
Product Code	06-059895-001
Package Contents	10
Units per Delivery	10/1

K7 Splice Cassette 2 Slots, Uni Zone-24+24

The CORNING logo is displayed in white, uppercase letters within a solid blue square.

Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.