

# MiniXtend® Cable, CT A-D(ZN)2Y, 4 fibres, CT, single-mode (SMF 28e® ULTRA) - VDE



**Part Number:**  
**004ZK4-13120ADE**

Corning MiniXtend products are fibre optic stranded loose tube or central tube fully dielectric outdoor cable typically used in access networks when limited space is available. With the dual layer tube design and low friction PE sheath MiniXtend cables are optimized for blowing and best used in mini or micro ducts.

The fibre in each tube are color-coded for quick and easy identification. MiniXtend are available with Corning® single-mode fibre SMF 28-e® (ITU-G 652D) or bend- improved ClearCurve® fibres (ITU-G 657 A/B).

## Features and Benefits

### **Improved cable and fibre density**

Reduced cable diameter for installation in micro ducts with 4mm minimum inner diameter

---

### **Fully-dielectric**

No grounding required

---

### **Optimised for air-assisted install in microducts**

Capable of installation distances greater than 2000 m (6560 ft) at speeds up to 150 m/min (490 ft/min)

---

### **SMF-28e+® according to ITU-T G.652.D**

Transmission security, low attenuation and polarization mode dispersion

# MiniXtend® Cable, CT A-D(ZN)2Y, 4 fibres, CT, single-mode (SMF 28e® ULTRA) - VDE

CORNING

## Specifications

General Specifications	
Installation Methods	Microduct
Cable type	Central Tube
Environment	Outdoor
Product type	Dielectric
Fibre category	Single-mode (OS2)
Cable geometry	Round

Standards	
Fibre Standards	TIA/EIA-492CAAB, IEC 60793-2-50 Type B1.3, ITU-T G.652.D and ITU-T G.657.A1, ISO/IEC 11801 Ed.2.2
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Environmental Conditions	
Temperature range, installation	-5 °C to 50 °C
Temperature range, operation	-20 °C to 60 °C
Temperature range, storage	-25 °C to 60 °C

Cable Design	
Cable marking	Meter Handset D-Sine CORNING Year MINIXTEND(R) A-D(ZN)2Y 4F E9U CT1.7
Fibre count	4
Outer jacket colour	Black
Outer jacket material	Polyethylene (PE)
Buffer tube diameter	1.75 mm
Cable marking method	Laser printing
Cable marking colour	White
Fibre colouring	Red, green, blue, yellow

# MiniXtend® Cable, CT A-D(ZN)2Y, 4 fibres, CT, single-mode (SMF 28e® ULTRA) - VDE



## Cable Design

Fibres per tube	4
-----------------	---

## Mechanical Specifications

Crush resistance	1000 N/10 cm
Max. tensile strength, short-term	80 N
Min. bend radius installation	20 mm
Nominal outer diameter	2.5 mm

## Optical Characteristics

Fibre code	Z
Performance option code	20
Fibre category	OS2
Fibre Type	Single-mode (OS2) / 250 µm
Fibre name	Bend-Improved Single-mode (OS2)
Maximum Attenuation	0.34 dB/km / 0.34 dB/km / 0.20 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fibre compliance	ITU-T G.652.D and ITU-T G.657.A1
Fibre core diameter	8.2 µm
Cladding diameter	125 µm
Coating diameter	242 µm
Dispersion @ 1550 nm	≤ 18 [ps/(nm*km)]
Dispersion @ 1625 nm	≤ 22 [ps/(nm*km)]
Cable cutoff wavelength	1260 nm
Mode-Field Diameter at 1310 nm	9.2 µm
Mode-Field Diameter at 1550 nm	10.4 µm
PMD Link Design Value	≤ 0.04 ps/√km
PMD (Polarization Mode Dispersion) maximum individual fibre	≤ 0.1 ps/√km

# MiniXtend® Cable, CT A-D(ZN)2Y, 4 fibres, CT, single-mode (SMF 28e® ULTRA) - VDE



Dimensions	
Cable Weight	4.5 kg/km
Max. cable length per reel/drum	6000 m



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany  
00 800 2676 4641 • FAX: • [www.corning.com/opcomm/emea](http://www.corning.com/opcomm/emea)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/emea/trademarks](http://www.corning.com/opcomm/emea/trademarks). Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.