

# EDGE8® Tap Module 1-Port, Conf A (LC-LC), SMF, 50/50 Split Ratio

CORNING

## Part Number: ETM8-50A-G

The EDGE8™ tap modules provide the same functionality as the EDGE8 connector modules with the added capability of monitoring of live traffic for various applications via the use of advanced splitter technology. The EDGE8 tap module provides significant data center space (and cost) savings by having the monitoring functionality contained within the module itself thereby eliminating the need for additional rack space.

## Features and Benefits

### Shuttered adapters

Creates one-hand operation while eliminating the need to remove and store dust caps

### VFL-compatible shutters

Decreases time needed to test and troubleshoot a link

### Key identifiers

8 on module and slider for easy identification as a Base-8 component

### Rear-loading capability

Decreases the time to prepare and install modules into fiber housings

### High density


Module enables 576 fibers in a 4U housing and 144 fibers in a 1U

### Low insertion loss performance

Improved performance specs allow for more mated pairs and/or longer link distances

### Universal wiring

Decreases complexity and risks associated with managing polarity during moves, adds and changes



# EDGE8® Tap Module 1-Port, Conf A (LC-LC), SMF, 50/50 Split Ratio

CORNING

## Specifications

### General Specifications

Product Type	Panels and Modules
Fiber Category	Bend-improved SM (OS2)
Application	Data Center

### Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

### Design

Fiber Count	4
Adapter Color Front	Blue / Red
Adapter Type Front	Shuttered LC
Housing Type	EDGE
Panel or Module Type	EDGE8
Number of Adapters per Panel	3

### Cable Design

Polarity	Straight-Through, TIA-568 Type-A
----------	----------------------------------

### Design - Adapter

Adapter Style	Shuttered
---------------	-----------

### Optical Specification - Hardware

Split Ratio Live/Tap	50/50
Wavelengths	1310 nm / 1550 nm

# EDGE8® Tap Module 1-Port, Conf A (LC-LC), SMF, 50/50 Split Ratio



Dimensions	
Width	5985 mm
Depth	1181 mm

Ordering Information	
Product Number	ETM8-50A-G
Package Contents	Modules packaged in individual blister packs.
Units per Delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany  
00 800 2676 4641 • FAX: • [www.corning.com/opcomm/emea](http://www.corning.com/opcomm/emea)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/emea/trademarks](http://www.corning.com/opcomm/emea/trademarks). Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.