

ALTOS® Loose Tube Dielectric Armour Outdoor Cable LT 2.0 HDPE, A-DQ(ZN)B2Y 8x12 E9 SMF-28e+® ITU G652.D

CORNING

Part Number:
096EPG-T3122P20

Corning glass-yarn armored loose tube cables are designed for outdoor use for campus, city and intercity backbones in duct installations.

The loose -tube cable construction, by isolating the fibres from installations and environmental rigors, provides stable and highly reliable transmission parameters. The 2.0 mm buffer tubes and fibres in each tube are color -coded for quick and easy identification.

The SZ-stranded construction further reduces installation and environmental influences on the transmission parameters and allows mid -span access.

These slim and lightweight cables are designed with a 1.1 mm HDPE outer jacket for easy installation in conduits and ducts.

Features and Benefits

Laminated glass yarns

For improved rodent resistance

All-dielectric cable construction

Requires no grounding or bonding

UV and microbe resistant

Can be installed in ducts

Waterblocking technology



OSP (outdoor) applications

Fibres/buffer tubes colour coded to Telcordia-Bellcore

Easy identification of the individual tubes and fibres

Dry cable core by means of water-swellable tape and elements

Allows efficient and craft-friendly cable preparation in outdoor or indoor/outdoor applications



ALTOS® Loose Tube Dielectric Armour Outdoor Cable LT 2.0 HDPE, A-DQ(ZN)B2Y 8x12 E9 SMF-28e+® ITU G652.D

CORNING

Specifications

General Specifications

Installation Methods	Duct
Cable type	Loose tube
Environment	Outdoor
Product type	Dielectric armour
Fibre category	Single-mode (OS2)
Coding according to EN 60794-1-1 (DIN VDE 0888-100-1)	A-DQ(ZN)B2Y
Cable geometry	Round

Standards

Fibre Standards	TIA/EIA-492CAAB, IEC 60793-2-50 Type B1.3, ITU-T G.652.D, ISO/IEC 11801 Ed.2.2
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	IEC 60794-3-10
Waterblocking	IEC 60794-1-2 F5

Environmental Conditions

Temperature range, installation	-5 °C to 70 °C
Temperature range, operation	-30 °C to 70 °C
Temperature range, storage	-40 °C to 70 °C

Cable Design

Cable marking	Metre - Handset - Sine - CORNING - Year - ALTOS (R) A-DQ(ZN)B2Y 8X12 E9 LT 2.0
Central element	Jacketed GRP
Fibre count	96
Number of ripcords	2
Buffer tube colour coding, layer 1	Blue, orange, green, brown, grey, white, red, black

ALTOS® Loose Tube Dielectric Armour Outdoor Cable LT 2.0 HDPE, A-DQ(ZN)B2Y 8x12 E9 SMF-28e+® ITU G652.D

CORNING

Cable Design

Outer jacket colour	Black
Outer jacket material	High Density Polyethylene (HDPE)
Outer jacket minimum thickness	1.1 mm
Outer jacket nominal thickness	1.1 mm
Buffer tube diameter	2 mm
Central element diameter	3.3 mm
Number of active tubes	8
Number of tube positions	8
Tensile strength elements and/or armouring	Laminated glass yarn armour
Fibre colouring	Blue, orange, green, brown, grey, white, red, black, yellow, violet, pink, turquoise
Fibres per tube	12
Colour Code Standards	Telcordia

Mechanical Specifications

Crush resistance	1500 N/10 cm
Max. tensile strength for installation	2700 N
Min. bend radius installation	198 mm
Min. bend radius operation	99 mm
Nominal outer diameter	9.9 mm

Optical Characteristics

Fibre code	E
Performance option code	22
Fibre category	OS2
Fibre Type	Single-mode (OS2) / 250 µm
Fibre name	Single-mode (OS2)
Maximum Attenuation	0.36 dB/km / 0.36 dB/km / 0.22 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm

ALTOS® Loose Tube Dielectric Armour Outdoor Cable LT 2.0 HDPE, A-DQ(ZN)B2Y 8x12 E9 SMF-28e+® ITU G652.D

CORNING

Optical Characteristics

Fibre compliance	ITU-T G.652.D
Fibre core diameter	8.2 µm
Cladding diameter	125 µm
Coating diameter	242 µm
Dispersion @ 1550 nm	≤ 18 [ps/(nm*km)]
Dispersion @ 1625 nm	≤ 22 [ps/(nm*km)]
Cable cutoff wavelength	1260 nm
Mode-Field Diameter at 1310 nm	9.2 µm
Mode-Field Diameter at 1550 nm	10.4 µm
PMD Link Design Value	≤ 0.06 ps/√km
PMD (Polarization Mode Dispersion) maximum individual fibre	≤ 0.1 ps/√km

Dimensions

Cable Weight	80 kg/km
Max. cable length per reel/drum	6000 m



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.