

MiniXtend® Cable, CT A-D(ZN)2Y, 6 fibres, CT, single-mode (E9 G.657.A1), DIN VDE



Part Number:
006ZK4-13122ADE

Corning MiniXtend products are fibre optic stranded loose tube or central tube fully dielectric outdoor cable typically used in access networks when limited space is available. With the dual layer tube design and low friction PE sheath MiniXtend cables are optimized for blowing and best used in mini or micro ducts.

The fibre in each tube are color-coded for quick and easy identification. MiniXtend are available with Corning® single-mode fibre SMF 28-e® (ITU-G 652D) or bend-improved ClearCurve® fibres (ITU-G 657 A/B).

Features and Benefits

Improved cable and fibre density

Reduced cable diameter for installation in micro ducts with 4mm minimum inner diameter

Fully-dielectric

No grounding required

Optimised for air-assisted install in microducts

Capable of installation distances greater than 2000 m (6560 ft) at speeds up to 150 m/min (490 ft/min)

SMF-28e+® according to ITU-T G.652.D

Transmission security, low attenuation and polarization mode dispersion

MiniXtend® Cable, CT A-D(ZN)2Y, 6 fibres, CT, single-mode (E9 G.657.A1), DIN VDE

CORNING

Specifications

General Specifications

Cable type	Central Tube
Product type	Dielectric
Fibre category	SMF-28® Ultra
Coding according to EN 60794-1-1 (DIN VDE 0888-100-1)	A-D(ZN)2Y
Cable geometry	Round

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Environmental Conditions

Temperature range, installation	-5 °C to 50 °C
Temperature range, operation	-20 °C to 60 °C
Temperature range, storage	-25 °C to 60 °C

Cable Design

Fibre count	6
Outer jacket colour	Black
Outer jacket material	Polyethylene (PE)
Buffer tube diameter	1.75 mm
Cable marking method	Laser printing
Fibre colouring	Blue, orange, green, brown, grey
Colour Code Standards	DIN VDE

Mechanical Specifications

Crush resistance	1000 N/10 cm
------------------	--------------

MiniXtend® Cable, CT A-D(ZN)2Y, 6 fibres, CT, single-mode (E9 G.657.A1), DIN VDE

CORNING

Mechanical Specifications

Crush resistance (reversible), outdoor cable	500 N/10 cm
Max. tensile strength, short-term	80 N
Min. bend radius installation	90 mm
Min. bend radius operation	50 mm
Min. Duct Size Diameter	3.5 mm
Optimal Duct Size	4 mm

Optical Characteristics

Fibre code	Z
Performance option code	22
Fibre category	OS2
Fibre Type	Single-mode (OS2) / 250 µm
Fibre name	Bend-Improved Single-mode (OS2)
Maximum Attenuation	0.34 dB/km / 0.34 dB/km / 0.22 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fibre compliance	ITU-T G.652.D and ITU-T G.657.A1

Dimensions

Cable Weight	4.5 kg/km
Max. cable length per reel/drum	6000 m



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.