

Building Access Terminal (BAT) Size S, grey, EMKA lock, 2 splice trays with 2 heatshrink and crimp splice holders



Part Number:
BAT-SGE-ST001

The Building Access Terminal (BAT) is available in sizes XS (Small Floor Terminal), S, M, L, XL to address different capacity requirements. It is offered in white or grey color and lockable with a Screw- or EMKA-Lock.

Features and Benefits

Can be locked with lock or screw (M4)

Plastic FRNC

White or grey colour

Cover completely removable


Clip to store documents

Side walls shaped to ensure maximum freedom of accessibility

Strain-relief for cables up to 12mm diameter

Modular configurable and extendable

Integrated channel to reduce installation time



Building Access Terminal (BAT), Size S, grey, EMKA lock, 2 splice trays with 2 heatshrink and crimp splice holders



Building Access Terminal (BAT), Size S, grey, EMKA lock, 2 splice trays with 2 heatshrink and crimp splice holders

Building Access Terminal (BAT) Size S, grey, EMKA lock, 2 splice trays with 2 heatshrink and crimp splice holders



Specifications

General Specifications	
Suitable for	250 µm and 900 µm bare fibres
Product type	Housings
Environment	Indoor/Outdoor
Mounting Type	Wall-mount

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Environmental Conditions	
Temperature range, installation	-5 °C to 50 °C
Temperature range, operation	-20 °C to 60 °C
Temperature range, storage	-25 °C to 70 °C

Building Access Terminal (BAT) Size S, grey, EMKA lock, 2 splice trays with 2 heatshrink and crimp splice holders



Design	
Lockable	Yes
Housing material	Composite and PC ABS
Additional cable number reached w/accessories	4
Max. cable number in basic unit w/accessories	3
Number of blank modules	1
Cable entry type	Grommeted slot
Number of pigtails	3
Number of splice trays	2
Pigtail length	2 m
Adapter type front	LC duplex
Colour	Light basic, RAL 7035
Pigtail type	Individual with natural primary coating and yellow secondary coating
Number of adapters	4

Design - Adapter	
Adapter housing colour	Green
Keyed adapter	Yes
Shuttered adapter	No

Optical Specification - Hardware	
Pigtail insertion loss	0.35 dB

Specifications - Connector A	
Connector type	LC duplex

Building Access Terminal (BAT) Size S, grey, EMKA lock, 2 splice trays with 2 heatshrink and crimp splice holders

CORNING

Dimensions

Height	250 mm
Width	200 mm
Depth	50 mm
Weight	0.86 kg

Ordering Information

Product Number	BAT-SGE-ST001
Package contents	4 screws and 4 dowels
Shipping weight	0.86 kg
Shipping Height	77 mm
Shipping Width	280 mm
Shipping Depth	280 mm
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.