


Centrix® XL loaded housings 1U, 3 cassettes, 48 - LC UPC adapters with SF pigtails, 144 ports, splice with heat-shrink protection, DIN VDE

CORNING

Part Number:
CL1E4P48-A9-2RHV00

Centrix® XL housings provide industry-leading, ultra-high-density connectivity when combined with Centrix splice, patch, splitter, WDM, MTP®, and other configurations of pre-terminated cassettes. With the unique Centrix design, all cassettes are exchangeable – sliding into the housing to make real structured patch cable management possible, while providing unprecedented finger access without the need for tools or any other accessories. The various range of mounting brackets provide flexible installation options for 19- and 21-inch cabinet requirements. Centrix cabinets enable fast and easy installation of the housing through its quick-mount feature. Loaded housings enable faster network deployments through reduced installation time and reduced packaging. Easy cable deployment and quick installation features for the pre-connectorised housing in the Centrix cabinet ensure safe, on-demand enhancements of existing structures at maximum port density.



Centrix™ XL Loaded Housings, 1U, 3 cassettes, 48 - LC UPC adapters with SF pigtails, 144 ports, splice with heat-shrink protection, DIN VDE

Centrix® XL loaded housings 1U, 3 cassettes, 48 - LC UPC adapters with SF pigtails, 144 ports, splice with heat-shrink protection, DIN VDE

CORNING

Specifications

General Specifications

Product type	Housings
Environment	Indoor
Fibre category	Single-mode (OS2)
Mounting Type	Rack-mount
Application	Central Office, Data Centre

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Environmental Conditions

Temperature range, operation	-40 °C to 70 °C
------------------------------	-----------------

Design

Adapter colour front	Blue
Pigtail type	900 µm
Splice protectors type	Heat shrink
Number of ports	144
Colour Code Standards	DIN VDE

Specifications - Connector A

Connector type	LC UPC
Polish	UPC

Dimensions

Height	45 mm
--------	-------

Centrix® XL loaded housings 1U, 3 cassettes, 48 - LC UPC adapters with SF pigtails, 144 ports, splice with heat-shrink protection, DIN VDE

CORNING

Dimensions

Width	514 mm
Depth	290 mm
Weight	4.2 kg

Ordering Information

Product Number	CL1E4P48-A9-2RHV00
Height Unit	1 U
Shipping weight	4.5 kg
Shipping Height	55 mm
Shipping Width	550 mm
Shipping Depth	350 mm
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.