

Centrix® XL Cabinet System 2200x1050x300 mm, side walls, rear wall, metal doors, cable entry right, no bottom channel, assembled, crossconnect

CORNING

Part Number:
CXL-CAB-F221APMRANC

Centrix® XL single cabinets provide space for up to 120 Centrix cassettes, with a maximum capacity of 5,760 LC or 4,320 SC single-fibre ports. All functions are accessible from the front of the cabinet. Patch cord management enables in-cabinet cross-connects with a single patch cord length of 4 m. Feeder cables can enter the cabinet from the top and bottom.

The bottom channel function allows for easy routing of patch cords across cabinets in a row. The cabinet comes assembled for fast deployment.

Features and Benefits

Manageable High-Density

Provides up to 18,300 ports/m² (5760 LC ports per single frame) in full front access, enables efficient use of space in congested spaces while ensuring best organization of and access to single ports

Scalable Architecture

Modular 19" housings with cassettes, handling splice, patch, stubbed, pre-terminated, and passive optical devices (xWDM and splitters) options, offer flexibility and easy expansion

Advanced Patch Cord Management

Gravity loops with 4-meter patch cords, 10 jumper management hubs, and bottom channels ensure clean and efficient routing, helping to avoid cable clutter at overhead channels

Enhanced Security

Full protection against unauthorized access, with feeder cable entry from both top and bottom for flexible installation options



Centrix® XL Cabinet System, 2200x1050x300 mm, side walls, rear wall, metal doors, cable entry right, no bottom channel, assembled, crossconnect

Centrix® XL Cabinet System 2200x1050x300 mm, side walls, rear wall, metal doors, cable entry right, no bottom channel, assembled, crossconnect

CORNING

Specifications

General Specifications

Mounting Type	Cabinet-mount
Splice option	Yes
Application	Fiber to the Premises (FTTP)
Pre-terminated	No

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Dimensions

Height	2200 mm
Width	1050 mm
Depth	300 mm

Ordering Information

Product Number	CXL-CAB-F221APMRANC
Height Unit	40 U
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.