

Basic Fiber Optic Pigtail Kit, LSZH, 900 μm Single-mode, LSZH, SMF-28® Ultra OS2, LC UPC Simplex, Telcordia Standard, Short strip, 2 m

CORNING

Part Number:
FK12-000201G4Z33AA002M

Pigtails are used for non-permanent connections in patch panels, transmission equipment etc. Factory assembled pigtails allow for high quality termination of a network.

Features and Benefits

Global operations

Worldwide manufacturing facilities and end-to-end vertical integration across the entire process ensure reliable supply and mitigate trade barriers or supply disruptions

Flexible design options


Choice of materials for strength elements and fibre properties dependent on application requirements

Superior Performance Testing

Every termination is tested to ensure the highest in network performance

State-Of-The-Art Manufacturing Processes

Corning proprietary manufacturing processes and advanced technology result in unsurpassed product consistency



Basic Fiber Optic Pigtail Kits, LSZH, 900 μm Single-mode, LSZH, SMF-28® Ultra OS2, LC UPC Simplex, Telcordia Standard, Short strip, 2 m

Basic Fiber Optic Pigtail Kit, LSZH, 900 µm Single-mode, LSZH, SMF-28® Ultra OS2, LC UPC Simplex, Telcordia Standard, Short strip, 2 m

CORNING

Specifications

General Specifications

Flame rating	LSZH/FRNC
Fibre category	Single-mode (OS2)
Environment	Indoor
Application	Fiber to the Premises (FTTP), In-Building Network (IBN), Local Area Network (LAN), Central Office

Standards

Fibre Standards	ITU-T G.652.D and ITU-T G.657.A1
Reaction to Fire	Eca
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Intermateability	IEC 61754

Environmental Conditions

Temperature range, installation	-20 °C to 70 °C
Temperature range, operation	-20 °C to 70 °C

Design

Fibre count	1
Outer jacket material	LSZH/FRNC
Outer jacket colour	Yellow
Polarity	Straight-through, TIA-568 type-A
Fibres per port	1

Mechanical Characteristics

Strip length	150 mm
Nominal outer diameter	0.9 mm

Basic Fiber Optic Pigtail Kit, LSZH, 900 μm Single-mode, LSZH, SMF-28® Ultra OS2, LC UPC Simplex, Telcordia Standard, Short strip, 2 m



Mechanical Characteristics

Min. bend radius installation	20 mm
Min. bend radius operation	10 mm

Specifications - Connector A

Tensile strength jacketed cable	50 N
Durability	≤ 0.2 dB change, 1000 rematings, FOTP-21
Connector type	No connector
Boot type	Simplex

Specifications - Connector B

Polish	UPC
Insertion loss, max.	0.25 dB
Tensile strength jacketed cable	50 N
Durability	≤ 0.2 dB change, 500 rematings, FOTP-21
Boot colour	Blue
Connector type	LC UPC simplex
Ferrule material	Ceramic
Housing colour	Blue
Housing material	Composite
Boot type	Simplex
Reflectance	≤ -45 dB

Dimensions

Length	2 m
--------	-----

Ordering Information

Product Number	FK12-000201G4Z33AA002M
----------------	------------------------

Basic Fiber Optic Pigtail Kit, LSZH, 900 μm Single-mode, LSZH, SMF-28® Ultra OS2, LC UPC Simplex, Telcordia Standard, Short strip, 2 m



Ordering Information	
Packaging method	Box
Shipping Height	190 mm
Shipping Width	250 mm
Shipping Depth	380 mm
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.