

12-Fiber MTP® PRO Jumper 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), TIA-568 Type-B polarity, no pulling grip, LSZH, 10 m

CORNING

Part Number:
J757512QEZ-NB010M

EDGE™ MTP® PRO patch cords are used to create a connection between MTP adapter panels, conversion modules, and electronics, typically providing connectivity within the rack or the row. These cable assemblies feature a smaller (2.0 mm) outside diameter than traditional 12-fibre patch cords to improve finger access and reduce congestion and increase airflow in the horizontal and vertical rack space. EDGE 12-fibre MTP patch cords have the same connector size and cable footprint as LC duplex patch cords used today. The density, airflow, and cable management advantages of EDGE solutions was preserved as you migrate to higher data rates.

These patch cords are manufactured using Corning® CleanAdvantage™ technology and shipped with optimised dust caps, eliminating the need for cleaning and scoping prior to the initial field connection. They are built with MTP PRO push-pull connectors, allowing for a simple one-step colour-coded polarity change without removing the connector housing. The connector also provides the capability for field-friendly pinning configuration changes with safe handling of pins and easy colour identification while maintaining product integrity.

Features and Benefits

Slim round 2-fiber interconnect cable

Improves airflow and reduces congestion

MTP® PRO connectors


Allows for pinning and polarity changes in the field

Bend-improved fibre

Allows tighter cable bends for slack storage and routing, less risk of downtime due to pinched or bent cables

Corning® CleanAdvantage™ technology and optimised dust cap

Eliminates the need for scoping and cleaning prior to initial field connection



MTP® Jumper, 12F, 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), TIA-568 Type-B polarity, no pulling grip, LSZH, 10 m

12-Fiber MTP® PRO Jumper 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), TIA-568 Type-B polarity, no pulling grip, LSZH, 10 m

CORNING

Specifications

General Specifications

Flame rating	LSZH/FRNC
Fibre category	50 µm MM (OM4)
Cable Type	Interconnect

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Environmental Conditions

Temperature range, installation	0 °C to 50 °C
Temperature range, operation	-10 °C to 60 °C

Design

Fibre count	12
Outer jacket material	LSZH/FRNC
Fibre Type	Multimode

Mechanical Characteristics

Minimum bend radius	17 mm
Tensile strength	200 N
Crush resistance	750 N/10 cm

Optical Characteristics

Fibre code	T
Performance option code	98
Fibre category	OM4

12-Fiber MTP® PRO Jumper 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), TIA-568 Type-B polarity, no pulling grip, LSZH, 10 m

CORNING

Optical Characteristics	
Fibre Type	Multimode
Fibre name	50 µm MM (OM4)
Maximum Attenuation	2.8 dB/km / 1.0 dB/km
Wavelengths	850 nm / 1300 nm
Fibre compliance	IEC 60793-2-10
Fibre core diameter	50 µm
Cladding diameter	125 µm
Coating diameter	242 µm
Serial 1 gigabit ethernet	1000 m / 600 m
Serial 10 gigabit ethernet	550 m / -
Minimum effective modal bandwidth (EMB)	4700 MHz*km / -
Min. overfilled launch (OFL) bandwidth	3500 MHz*km / 500 MHz*km

Specifications - Connector A	
Reflectance, typical	< -20 dB
Polish	PC
Insertion loss, max.	0.35 dB
Note:	*IL in preconnectorized products is measured in the factory through two mated pairs.
Tensile strength jacketed cable	10 N
Durability	≤ 0.2 dB change, 200 rematings, FOTP-21
Boot colour	Turquoise
Connector type	MTP® (non-pinned)
Ferrule material	Composite
Housing colour	Black
Housing material	Composite
Boot type	Simplex

12-Fiber MTP® PRO Jumper 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), TIA-568 Type-B polarity, no pulling grip, LSZH, 10 m

CORNING

Specifications - Connector B

Reflectance, typical	< -20 dB
Polish	PC
Note:	*IL in preconnectorized products is measured in the factory through two mated pairs.
Tensile strength jacketed cable	10 N
Durability	≤ 0.2 dB change, 200 rematings, FOTP-21
Boot colour	Turquoise
Connector type	MTP® (non-pinned)
Ferrule material	Composite
Housing colour	Black
Housing material	Composite
Boot type	Simplex

Pulling grip - Connector B

Tensile strength	200 N
------------------	-------

Dimensions

Length	10 m
Outer diameter	2 mm
Weight	2 kg

Ordering Information

Product Number	J757512QEZ-NB010M
Packaging method	Cardboard box
Shipping Height	180 mm
Shipping Width	250 mm
Shipping Depth	380 mm
Units per delivery	1/1

12-Fiber MTP® PRO Jumper 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), TIA-568 Type-B polarity, no pulling grip, LSZH, 10 m

CORNING



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.