

LS Series Outdoor Cabinets 288 F Pole-mnt w/ toning, 24 F Feed and 12 Pass-thru, ALTOS® Arm., 1x288 F Dist ALTOS Arm., 50 m Stubs, SC APC, No Splitter



Part Number:
VCPPS21T1U5150U500

The OptiTect® Local Convergence Cabinet, LS Series provides everything necessary to manage up to 864 fibers for an outside plant FTTx application. The OptiTect Local Convergence Cabinet, LS Series is an innovative solution that is the optimal balance between size, density and access. All cabinets share the same intuitive and efficient cable routing and splitter storage. The LS cabinet was developed with the field craft in mind. In this unique cabinet design, splitter parking and cable toning are simple, providing customers more flexibility and deployment options. The best-in-class fiber routing design allows for quick subscriber turn-up and error-free long-term maintenance as the cabinet is loaded to capacity. All five cabinet sizes (144, 288, 432, 576, 864) offer “pass-through” capabilities for commercial services or other high-bandwidth applications, as well as multiple mounting options to accommodate exclusive below ground and aerial plant installations.

Features and Benefits

Multiple pad- and pole-mount configurations

Provide operator with maximum deployment flexibility

Unique grounding system

Provides a single point outside the cabinet to isolate and tone cables in the cabinet

Field-replaceable shell

Allows operator to replace outer hardware without interrupting services

Provides quick field placement and parking of splitter modules

Utilizes a 32-port connector clip

LS Series Outdoor Cabinets 288 F Pole-mnt w/ toning, 24 F Feed and 12 Pass-thru, ALTOS® Arm., 1x288 F Dist ALTOS Arm., 50 m Stubs, SC APC, No Splitter

CORNING

Specifications

General Specifications

Product Type	FTTx Cabinets
Mounting Type	Pole-mount
Application	Carrier Networks, CATV Environments

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Design and Test Criteria	Cabinets meet applicable sections of Telcordia GR-2898-CORE, GR-487-CORE, GR-63-CORE, GR-449-CORE

Design

Number of Distribution Cables	1x288
Cabinet Fiber Capacity	288
Distribution Cable Type	ALTOS® Loose Tube, Gel-Filled, Double-Jacket, Single-Armored
External Toning Option	Toning
Feeder or Pass Through Cable Type	ALTOS® Loose Tube, Gel-Filled, Double-Jacket, Single-Armored
Housing Type	LS Series Cabinets
Splitter module category	No splitter
Number of Fibers in Input Cable	24
Number of Pass Through Fibers	12

Design - Adapter

Adapter Type	SC APC
--------------	--------

LS Series Outdoor Cabinets 288 F Pole-mnt w/ toning, 24 F Feed and 12 Pass-thru, ALTOS® Arm., 1x288 F Dist ALTOS Arm., 50 m Stubs, SC APC, No Splitter

CORNING

Mechanical Specifications

Feeder and Distribution Cable Length	50 m
--------------------------------------	------

Connector Specs

Polish	APC
--------	-----

Ordering Information

Product Number	VCPPS21T1U5150U500
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.