

EDGE8® MTP® PRO Jumper 8F, 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), LSZH, TIA-568 Type-B polarity, no pulling grip, 3 m

CORNING

Part Number:
JE6E608QEZ-NB003M

EDGE8® 8-fiber MTP® PRO jumpers allow for seamless migration to higher data rates in the data center when used in conjunction with EDGE8 trunks. These assemblies have the same connector size and cable footprint as duplex LC jumpers. The density, airflow, and cable management advantages of EDGE8 solutions are preserved as you migrate to higher data rates.

These MTP Jumpers are built utilizing MTP PRO connectors. MTP PRO allows for a simple, one-step, color-coded polarity change without removing the connector housing. The connector also provides the capability for field-friendly pinning configuration changes with safe handling of pins and easy color identification while maintaining product integrity.

EDGE8 MTP jumpers are manufactured with Corning® CleanAdvantage™ and shipped with optimized dust caps, eliminating the need for cleaning and scoping prior to initial field connection.

For polarity guidance, reference applications engineering note AEN156.

Features and Benefits

Slim round 2-fiber interconnect cable

Improves airflow and reduces congestion

MTP® PRO connectors


Allows for pinning and polarity changes in the field

Bend-improved fiber

Allows tighter cable bends for slack storage and routing, less risk of downtime due to pinched or bent cables

Corning® CleanAdvantage™ technology and optimized dust cap

Eliminates the need for scoping and cleaning prior to initial field connection



EDGE8® MTP® Jumper, 8F, 50 µm multimode (OM4), MTP PRO (non-pinned) to MTP PRO (non-pinned), LSZH, TIA-568 Type-B polarity, no pulling grip, 3 m

EDGE8® MTP® PRO Jumper 8F, 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), LSZH, TIA-568 Type-B polarity, no pulling grip, 3 m

CORNING

Specifications

General Specifications

Flame Rating	LSZH/FRNC
Fiber Category	Bend-improved 50 µm MM (OM4)
Cable Assembly Type	EDGE8 Jumper
Cable Type	Interconnect
Assembly Insertion Loss	≤ 0.5 dB

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Intermateability	TIA/EIA-604-5 / TIA/EIA-604-5

Environmental Conditions

Temperature Range, Installation	0 °C to 50 °C (32 °F to 122 °F)
Temperature Range, Operation	-10 °C to 60 °C (14 °F to 140 °F)

Design

Fiber Count	8
Polarity	TIA-568 Type-B

Mechanical Specifications

Nominal Outer Diameter	2 mm
Max. Tensile Strength for Installation	220 N
Min. Bend Radius Installation	30 mm
Min. Bend Radius Operation	10 mm

EDGE8® MTP® PRO Jumper 8F, 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), LSZH, TIA-568 Type-B polarity, no pulling grip, 3 m

CORNING

Optical Characteristics

Fiber Code	T
Performance Option Code	98
Fiber Category	OM4
Fiber Type	Multimode
Fiber Name	50 µm MM (OM4)
Maximum Attenuation	2.8 dB/km / 1.0 dB/km
Wavelengths	850 nm / 1300 nm
Fiber Compliance	IEC 60793-2-10
Fiber Core Diameter	50 µm
Cladding diameter	125 µm
Coating diameter	242 µm
Serial 1 Gigabit Ethernet	1000 m / 600 m
Serial 10 Gigabit Ethernet	550 m / -
Minimum Effective Modal Bandwidth (EMB)	4700 MHz*km / -
Min. Overfilled Launch (OFL) Bandwidth	3500 MHz*km / 500 MHz*km

Specifications - Connector A

Polish	UPC
Insertion Loss, Max.	0.35 dB
Note:	*IL in preconnectorized products is measured in the factory through two mated pairs.
Boot Color	Black
Connector Type	MTP® (non-pinned)
Ferrule Material	Composite
Boot Type	Simplex
Reflectance	< -20 dB

Specifications - Connector B

Insertion Loss, Max.	0.35 dB
----------------------	---------

EDGE8® MTP® PRO Jumper 8F, 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), LSZH, TIA-568 Type-B polarity, no pulling grip, 3 m

CORNING

Specifications - Connector B

Note:	*IL in preconnectorized products is measured in the factory through two mated pairs.
Connector Type	MTP® (non-pinned)
Ferrule Material	Composite
Reflectance	< -20 dB

Dimensions

Length	3 m
Cable Weight	9 kg/km

Ordering Information

Product Number	JE6E608QEZ-NB003M
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.