

# Front Access Breakout Module 8 F, LC duplex to front access non-pinned MTP® connector, bend-improved Single-mode (OS2)

CORNING

**Part Number:**  
**ECM-UM08-04-E8GF-ULL**

This module will typically connect to the active electronics, via a jumper or harness, and break out the 8-fiber QSFP 40G transceiver into 4x 2-fiber 10G LC duplex connections.

The module has an EDGE™ footprint for easy integration in a Base-12 solution. Its all-front access to the adapters make it ideal for deployments where space and access are challenging.

## Features and Benefits

### VFL-compatible shuttered LC adapters

Creates one-hand operation and decreases time needed to test and troubleshoot a link

### Rear-loading capability

Decreases the time to prepare and install modules into fiber housings

### High density


Module enables 576 fibers in a 4U housing and 144 fibers in a 1U

### Low insertion loss performance

Improved performance specs allow for more mated pairs and/or longer link distances

### Corning® CleanAdvantage™ technology and optimized dust cap

Eliminates the need for scoping and cleaning prior to initial field connection



Front Access Breakout Module, 8 F, LC duplex to front access non-pinned MTP® connector, bend-improved Single-mode (OS2)

# Front Access Breakout Module 8 F, LC duplex to front access non-pinned MTP® connector, bend-improved Single-mode (OS2)

CORNING

## Specifications

### General Specifications

|                |                        |
|----------------|------------------------|
| Product Type   | Panels and Modules     |
| Fiber Category | Bend-improved SM (OS2) |
| Application    | Data Center            |

### Standards

|      |                                                           |
|------|-----------------------------------------------------------|
| RoHS | Free of hazardous substances according to RoHS 2011/65/EU |
|------|-----------------------------------------------------------|

### Design

|                              |                            |
|------------------------------|----------------------------|
| Fiber Count                  | 8                          |
| Adapter Color Front          | Blue / Black               |
| Adapter Type Front           | LC duplex/MTP (non-pinned) |
| Housing Type                 | Panels and Modules         |
| Panel or Module Type         | EDGE8                      |
| Number of Adapters per Panel | 4                          |

### Cable Design

|          |           |
|----------|-----------|
| Polarity | Universal |
|----------|-----------|

### Optical Specification - Hardware

|             |                   |
|-------------|-------------------|
| Wavelengths | 1310 nm / 1550 nm |
|-------------|-------------------|

### Dimensions

|       |       |
|-------|-------|
| Width | 90 mm |
| Depth | 12 in |

Front Access Breakout Module 8 F, LC duplex to front access non-pinned MTP® connector, bend-improved Single-mode (OS2)



| Ordering Information |                                               |
|----------------------|-----------------------------------------------|
| Product Number       | ECM-UM08-04-E8GF-ULL                          |
| Package Contents     | Modules packaged in individual blister packs. |
| Units per Delivery   | 1/1                                           |



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/emea/trademarks](http://www.corning.com/opcomm/emea/trademarks). Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.