

SST-Ribbon Single-Tube, Gel-Free Cable 48 F, Bend-improved Single-mode (OS2)

CORNING

Part Number:
048ZC4-14100D53

Corning SST-Ribbon gel-free cables represent a truly innovative breakthrough in outside plant cable technology. Providing up to 216 fibers in a compact design, the enhanced coupling features ensure the ribbon stack and cable act as one unit, providing long-term reliability in aerial, duct and direct-buried applications. These features also minimize ribbon movement in situations where cable vibration may occur. The cable consists of a single buffer tube containing a stack of up to eighteen 12-fiber ribbons wrapped within a water-swellable foam tape and surrounded by a second water-swellable tape. Dielectric strength members located 180 degrees apart under the cable jacket provide tensile and anti-buckling strength. The cable is jacketed with a black UV-resistant polyethylene sheath. The 12-fiber ribbons have readily identifiable ribbon IDs and fiber colors and geometries that result in excellent mass-splicing yields.

Features and Benefits

Gel-free waterblocking technology

Craft-friendly cable preparation

Innovative waterblocking technology



Prevents water penetration

12-fiber ribbons with ribbon IDs

Easy identification

Up to 216 fibers in a compact design

Easily fits in 1.0 inch inner diameter duct



SST-Ribbon Single-Tube, Gel-Free Cable 48 F, Bend-improved Single-mode (OS2)

CORNING

Specifications

General Specifications

Installation Methods	Aerial, Duct, Direct Buried
Cable Type	Ribbon
Environment	Outdoor
Product Type	Dielectric
Fiber Category	SMF-28® Ultra
Cable geometry	Round

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Common Installations	Outdoor lashed aerial and duct, indoor when installed according to National Electrical Code® (NEC®) Article 770
Design and Test Criteria	ANSI/ICEA S-87-640, Telcordia GR-20, RDUP PE-90

Environmental Conditions

Temperature Range, Installation	-30 °C to 70 °C (-22 °F to 158 °F)
Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
Temperature Range, Storage	-40 °C to 70 °C (-40 °F to 158 °F)

Cable Design

Buffer Tube Color	Natural
Fiber Count	48
Buffer Tube Diameter	5.6 mm (0.22 in)
Number of Ripcords	2
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Outer Jacket Color	Black
Outer Jacket Material	Polyethylene (PE)

SST-Ribbon Single-Tube, Gel-Free Cable 48 F, Bend-improved Single-mode (OS2)

CORNING

Cable Design

Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Tape	Water-swellable
Tape, Layer 1	Water-swellable
Tape, Layer 2	Water-swellable
Ribbons per Tube	4
Fibers per Ribbon	12

Mechanical Specifications

Max. Tensile Strength, Long-Term	890 N (200.08 lbf)
Max. Tensile Strength, Short-Term	2700 N (606.98 lbf)
Min. Bend Radius Installation	156 mm (6.14 in)
Min. Bend Radius Operation	104 mm (4.09 in)
Nominal Outer Diameter	10.4 mm (0.41 in)
Min. Bend Diameter Operation	208 mm (8.19 in)
Min. Bend Diameter Installation	312 mm (12.28 in)

Optical Characteristics

Fiber Code	Z
Performance Option Code	00
Fiber Category	OS2
Fiber Type	Single-mode (OS2) / 250 µm
Fiber Name	Bend-Improved Single-mode (OS2)
Maximum Attenuation	0.35 dB/km / 0.35 dB/km / 0.25 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Compliance	ITU-T G.652.D and ITU-T G.657.A1

Dimensions

Cable Weight	84 kg/km (56.45 lb/1000 ft)
--------------	-----------------------------

SST-Ribbon Single-Tube, Gel-Free Cable 48 F, Bend-improved Single-mode (OS2)

The Corning logo consists of the word "CORNING" in white, uppercase, sans-serif font, centered within a solid blue square.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.