

SST-UltraRibbon Single-Tube, Gel-Free Cable 576 F, Bend-improved Single-mode (OS2)

CORNING

Part Number:
576ZV4-14100D53

Corning SST-UltraRibbon gel-free cables continue the innovative breakthrough in outdoor cable technology by introducing a new generation of high-fiber-count gel-free cables. Providing high-fiber-counts in a rugged, compact design, the enhanced coupling features ensure the ribbon stack and cable act as one unit, providing long-term reliability in aerial, duct and direct-buried applications. These features also minimize ribbon movement in situations where cable vibration may occur. The cable consists of a single buffer tube containing 24-fiber and 36-fiber ribbons wrapped within a water-swellable foam tape and surrounded by a second water-swellable tape. Each 24-fiber and 36-fiber ribbon can be easily separated by hand into 12-fiber ribbons. Strength members located 180 degrees apart under the cable jacket provide tensile and anti-buckling strength. The cable is jacketed with a black UV-resistant polyethylene sheath.


Features and Benefits

Gel-free with no filling compound
Eliminates time and labor of cleaning


Innovative waterblocking technology
Prevents water penetration

Up to 864 fibers in a compact design
Maximizes use of critical duct space

12-fiber ribbons individually numbered
Easy identification



SST-UltraRibbon Single-Tube, Gel-Free Cable, 576 F, Bend-improved Single-mode (OS2)



SST-UltraRibbon Single-Tube, Gel-Free Cable, 576 F, Bend-improved Single-mode (OS2)

SST-UltraRibbon Single-Tube, Gel-Free Cable 576 F, Bend-improved Single-mode (OS2)

CORNING

Specifications

General Specifications

Installation Methods	Aerial, Duct
Fiber Category	SMF-28® Ultra
Cable geometry	Round

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Cable Design

Fiber Count	576
Ribbons per Tube	12 and 6
Fibers per Ribbon	24

Mechanical Specifications

Max. Tensile Strength, Long-Term	890 N (200.08 lbf)
Max. Tensile Strength, Short-Term	2700 N (606.98 lbf)
Nominal Outer Diameter	23.4 mm (0.92 in)
Min. Bend Diameter Operation	468 mm (18.43 in)
Min. Bend Diameter Installation	702 mm (27.64 in)

Optical Characteristics

Fiber Code	Z
Performance Option Code	00
Fiber Category	OS2
Fiber Type	Single-mode (OS2) / 250 µm
Fiber Name	Bend-Improved Single-mode (OS2)

SST-UltraRibbon Single-Tube, Gel-Free Cable 576 F, Bend-improved Single-mode (OS2)

CORNING

Optical Characteristics

Maximum Attenuation	0.35 dB/km / 0.35 dB/km / 0.25 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Compliance	ITU-T G.652.D and ITU-T G.657.A1

Dimensions

Cable Weight	330 kg/km (221.75 lb/1000 ft)
--------------	-------------------------------



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.