

Edge Uniboot Jumper Standard LCU Uniboot SM / Standard LCU Uniboot SM, SMF Ultra, 2F, DFX 250 Riser, Standard Yellow Jacket 8 Meters

CORNING

Part Number:
787802GD120008M

EDGE™ Reverse Polarity Uniboot Duplex Jumpers allow for the quick and easy conversion from a TIA-568 A-B polarity to a TIA-568 A-A polarity without exposing the fibers or needing any tools. This jumper comes with a straight-through polarity from the factory, but you can convert it to a flipped jumper. This uniboot design allows one cable to carry both fibers, reducing the jumper bulk when routing.

This product is available for Quick Connect 48 hour shipping. Learn more here:

[Quick Connect Program](#)

Features and Benefits

State-of-the-art manufacturing processes

Advanced technology results in unsurpassed product consistency and quality

Global operations

Worldwide manufacturing facilities and end-to-end vertical integration across the entire process ensure reliable supply and mitigate trade barriers or supply

Flexible design options


Choice of materials for strength elements and fiber properties for various application requirements

Superior performance testing

Each termination is tested to ensure the highest network performance

Space reducing design

The uniboot design allows one cable to carry both fibers, reducing the jumper bulk when routing



Edge Uniboot Jumper Standard LCU Uniboot SM / Standard LCU Uniboot SM, SMF Ultra, 2F, DFX 250 Riser, Standard Yellow Jacket 8 Meters



Specifications

General Specifications	
Flame Rating	Riser (OFNR)
Fiber Category	Bend-improved SM (OS2)
Cable Assembly Type	Two Fiber
Application	Data Center
Cable Type	Interconnect
Installation Methods	General Building Applications, Riser

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Design	
Fiber Count	2
Outer Jacket Color	Yellow
Fiber Type	Single-Mode Ultra-Bendable Fiber

Mechanical Specifications	
Minimum Bend Radius	10 mm (0.39 in)
Nominal Outer Diameter	2 mm (0.08 in)

Optical Characteristics	
Fiber Code	Z
Performance Option Code	01
Fiber Category	OS2
Fiber Type	Single-mode (OS2) / 250 μ m
Fiber Name	Bend-Improved Single-mode (OS2)

Edge Uniboot Jumper Standard LCU Uniboot SM / Standard LCU Uniboot SM, SMF Ultra, 2F, DFX 250 Riser, Standard Yellow Jacket 8 Meters



Optical Characteristics	
Maximum Attenuation	0.4 dB/km / 0.4 dB/km / 0.3 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Compliance	ITU-T G.652.D and ITU-T G.657.A1

Specifications - Connector A	
Polish	UPC
Boot Color	Blue
Connector Type	LC Uniboot
Ferrule Material	Ceramic
Housing Color	Blue
Housing Material	Composite

Specifications - Connector B	
Polish	UPC
Boot Color	Blue
Connector Type	LC Uniboot
Ferrule Material	Ceramic
Housing Color	Blue

Dimensions	
Length	8 m (26.24 ft)

Ordering Information	
Product Number	787802GD120008M
Units per Delivery	1/1

Edge Uniboot Jumper Standard LCU Uniboot SM / Standard LCU Uniboot SM, SMF Ultra, 2F, DFX 250 Riser, Standard Yellow Jacket 8 Meters

CORNING



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.