

Integrated 1U Housing 48 F, rear-mounted OptiTip® Adapters, front-mounted LC duplex Adapters, Single-mode (OS2)



CORNING

Part Number:
CC1-48OTR-48A9H

Corning Integrated 1U housing utilizes the OptiTip® adapter with a 1U rack-mountable housing for quick and easy deployment, eliminating the need for field-terminated and strain-relieved fiber optic cables. The housing is ideal for star, ring, point-to-point or zone architectures. The factory-terminated housing provides industry-leading quality and reliability while eliminating the time required for field-termination methods.

Many of our fiber optic hardware products are highly configurable. If you don't see what you are looking for here, please review the ordering matrix contained in the family spec sheet found on the right, or contact Customer Care at 1-800-743-2675.

Features and Benefits

Factory terminated

Eliminates need for field termination, improving reliability and speed of deployment

Configurable in 12 and 24 fibers, single-mode and multimode, supporting SC, LC and ST® compatible connectors

Network flexibility

Integrated 1U Housing 48 F, rear-mounted OptiTip® Adapters, front-mounted LC duplex Adapters, Single-mode (OS2)

CORNING

Specifications

General Specifications

Product Type	Housings
Fiber Category	Single-mode (OS2)
Mounting Type	Rack-mount
Application	Enterprise Networks

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Fiber Count	48
Housing Type	Integrated Housing
OptiTip® Adapter Placement	Rear-mounted

Cable Design

Fiber Count	48
-------------	----

Design - Adapter

Adapter Style	Standard
Adapter Type	LC duplex

Connector Specs

Polish	UPC
--------	-----

Integrated 1U Housing 48 F, rear-mounted OptiTip® Adapters, front-mounted LC duplex Adapters, Single-mode (OS2)

CORNING

Specifications - Connector A

Connector Type	LC duplex
Polish	UPC

Dimensions

Height	440 cm
Width	45.5 cm
Depth	246 cm

Ordering Information

Product Number	CC1-48OTR-48A9H
Package Contents	Housing; installation guide with cleaning kit guide; unit ID label; 2 jumper routing guides, 0.75 in and 4 #12-24 x 50 screws
Shipping Weight	2 kg
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.