

CCH Cassette Pass-Through Splicing Applications

CORNING

Part Number: CCH-CS-PST

CCH pass-through cassettes enable through splicing of fibers when any housing that accommodates the CCH Cassette.

Each cassette is shipped with one rail for use with CCH-01U/2U/3U housings and two rails used with CCH-04U and the WCH-02P/4P/6P housings. Grommets and cable ties for strain relief, and protective braided tubing for incoming cable are also included. Splicing cassettes ship with 12 single-fiber heat-shrink splice protectors.

CCH-CS-PST is for through splicing applications only and does not accept a CCH adapter panel.

Features and Benefits

Pass-through cassette holds 24 single-fiber splices or 6 mass fusion splices

Splice to full housing capacity and manage all splices inside the housing

Includes everything needed to convert a CCH housing for modular routing and/or splicing

Easy ordering and field installation

Manage cable slack for a CCH panel in a modular footprint

Fast, easy and reliable initial routing, and quick, simple reaccess for moves, adds and changes (MACs)



CCH Cassette Pass-Through Splicing Applications

CORNING



CCH Cassette, Pass-Through Splicing Applications



CCH Cassette, Pass-Through Splicing Applications

Specifications

General Specifications

Product Type	Rack-Mountable Hardware
Technology	Fusion Splice
Mounting Type	Rack 19-in, Rack 23-in, Wall-Mountable
Application	Data Center, Enterprise Networks

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	Meets ANSI/TIA/EIA-568A and 606

Environmental Conditions

Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
------------------------------	-------------------------------------

CCH Cassette Pass-Through Splicing Applications

CORNING

Design

Housing Type	Rack-Mountable Hardware
Panel or Module Type	CCH

Ordering Information

Product Number	CCH-CS-PST
Shipping Weight	0.5 kg
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.