

Evolv® SST-Drop™ with Pushlok® Technology 6F Pushlok to 6F MTP Angled Connector, Dielectric with Pulling Grip, 150 ft, Individual Packaging

CORNING

Part Number:
D19006JBP43150F-P

As an industry leader in optical connectivity products, Corning designs and manufactures the SST-Drop™ cable assembly with factory-terminated, environmentally sealed and hardened connectors to reduce the cost and the time of drop cable deployment in optical access networks. The Pushlok® drop cable assembly is specifically designed to significantly reduce required drop cable installation.

Features and Benefits

Hardened connector technology


Reduced-diameter Pushlok® connector

Flexible connector offerings

2 & 4 Multifiber drops including pigtail small cell and inline variants available 2F small cell variants with a Pushlok hardened connector to LC or Uniboot

Versatile installation environments

Dielectric and toneable variants available



Evolv® SST-Drop™ with Pushlok® Technology, 6F Pushlok to 6F MTP Angled Connector, Dielectric with Pulling Grip, 150 ft, Individual Packaging

Evolv® SST-Drop™ with Pushlok® Technology 6F Pushlok to 6F MTP Angled Connector, Dielectric with Pulling Grip, 150 ft, Individual Packaging

CORNING

Specifications

General Specifications

Cable Type	SST-Drop™ dielectric
Packaging	Individual Pack

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Fiber Count	6
-------------	---

Optical Characteristics

Fiber Code	J
Performance Option Code	01
Fiber Category	OS2
Fiber Type	Single-mode (OS2) / 250 µm
Fiber Name	ClearCurve® LBL
Maximum Attenuation	0.4 dB/km / 0.4 dB/km / 0.30 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Compliance	ITU-T G.652.D and ITU-T G.657.A2/B2

Specifications - Connector A

Insertion Loss, Max.	0.4 dB
Connector Type	Pushlok
Reflectance	≤ -65 dB

Evolv® SST-Drop™ with Pushlok® Technology 6F Pushlok to 6F MTP Angled Connector, Dielectric with Pulling Grip, 150 ft, Individual Packaging

CORNING

Specifications - Connector B

Insertion Loss, Max.	0.3 dB
Connector Type	MTP®
Reflectance	≤ -65 dB

Dimensions

Length	150 ft
--------	--------

Ordering Information

Product Number	D19006JBP43150F-P
Packaging Method	Box
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.