

GEN III Series Indoor Cabinets 144 F, wall-mount, 12 F feeder 31 m FREEDM® SST-ribbon cable, 144 F distribution ribbon pigtails SC APC, no splitter



Part Number:
BDWP131CF-S00

The OptiTect® Indoor Local Convergence Cabinet, Gen III Series family delivers everything needed to distribute up to 432 distribution fibers for FTTx applications. All cabinets feature intuitive fiber management and internal layout that minimize training time and optimize installer productivity. Feeder fibers, distribution fibers, splitter modules, splitter input splicing, and unused splitter output storage are contained within a single, rugged, wall- or rack-mountable enclosure. Factory preconnectorization and installation of feeder and riser cables, or splice capability, ensure quick, easy, and reliable installation in the field. The cabinet features an innovative swing-out panel for rear connector access and an integrated storage door for parking unused splitter module output connectors.

The OptiTect Indoor Local Convergence Cabinet, Gen III Series is available in multiple configurations. It can be purchased pigtailed, fully stubbed, or partially stubbed.

Features and Benefits

Rugged, low-profile, wall- or rack-mountable (wall- or rack-mount hardware included with each cabinet)

Integrated splitter parking door for unused splitter output connectors

Swing-out panel allows for rear connector access

Intuitive single-fiber slack storage routing schemes

216-B door lock with padlock provisions

GEN III Series Indoor Cabinets 144 F, wall-mount, 12 F feeder 31 m FREEDM® SST-ribbon cable, 144 F distribution ribbon pigtails SC APC, no splitter

CORNING

Specifications

General Specifications

Product Type	Multidwelling Unit (MDU) Hardware
Mounting Type	Wall-Mountable
Application	Carrier Networks, CATV Environments

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Number of Distribution Cables	144
Cabinet Fiber Capacity	144
Distribution Cable Type	Ribbon Pigtails
Feeder or Pass Through Cable Type	FREEDM® SST-Ribbon Cable
Housing Type	Multidwelling Unit (MDU) Hardware
Splitter module category	No splitter
Number of Fibers in Input Cable	12

Design - Adapter

Adapter Type	SC APC
--------------	--------

Mechanical Specifications

Feeder Cable Length	31 m (101.68 ft)
---------------------	------------------

Connector Specs

Polish	APC
Housing Color	Almond

**GEN III Series Indoor Cabinets 144 F, wall-mount,
12 F feeder 31 m FREEDM® SST-ribbon cable, 144
F distribution ribbon pigtails SC APC, no splitter**



Specifications - Connector A	
Housing Color	Almond

Ordering Information	
Product Number	BDWP131CF-S00
EAN Code	4056418195155
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm