


# Plug & Play™ Base-8 Module 24 F, shuttered LC to non-pinned MTP® connector, bend-improved Single-mode (OS2)



**Part Number:**  
**CCH8-UM24-04-E8G-ULL**

The 24-fiber MTP® to LC duplex module is ideal for customers that want to deploy a Base-8 solution in an existing CCH or PCH infrastructure.



Plug & Play™ Base-8 Module, 24 F, shuttered LC to non-pinned MTP® connector, bend-improved Single-mode (OS2)

# Plug & Play™ Base-8 Module 24 F, shuttered LC to non-pinned MTP® connector, bend-improved Single-mode (OS2)



## Specifications

General Specifications	
Product Type	Panels and Modules
Fiber Category	Bend-improved SM (OS2)
Application	Data Center

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Design	
Fiber Count	24
Adapter Type Back	MTP® (non-pinned)
Adapter Color Back	Black
Adapter Color Front	Blue
Adapter Type Front	Shuttered LC
Housing Type	Modules
Panel or Module Type	CCH

Cable Design	
Polarity	Universal

Optical Specification - Hardware	
Wavelengths	1310 nm / 1550 nm

Ordering Information	
Product Number	CCH8-UM24-04-E8G-ULL
Units per Delivery	1/1

# Plug & Play™ Base-8 Module 24 F, shuttered LC to non-pinned MTP® connector, bend-improved Single-mode (OS2)

CORNING



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.