


Centrix™ XL Splice Cassette 48 Fiber, LC UPC, Single-mode (OS2), Single Fiber

CORNING

Part Number:
CTXLCPP48-A9-2RH000

The Centrix™ XL splice cassette provides up to 48 LC or 36 SC single fiber ports. The cassette is loaded with Duplex adapters, colored single fiber pigtails and accepts crimp or heat-shrink splice protectors. A drop handle provides fiber port protection, patch cord organization and labeling on front and top of the cassette. The cassette is slidable in Centrix XL housings and is secured with a latch mechanism. The jumper guide direction is to the left side of the cassette but can simply be changed with accessories to the right. The transparent and captive top and bottom cover enable easy handling and visual inspection or trouble shooting. The multiple tube entry points on the cassette provide flexible loading of buffer tubes and bare fibers in the cassette.



Centrix™ XL Splice Cassette 48 Fiber, LC UPC, Single-mode (OS2), Single Fiber



Specifications

General Specifications	
Product Type	Splice cassettes
Fiber Category	Single-mode (OS2)

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Environmental Conditions	
Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)

Design	
Pigtail Type	900 µm
Splice Protectors Type	Not Available
Number of Ports	48
Color Code Standards	Telcordia

Design - Adapter	
Housing Color	Blue
Adapter Type	LC UPC

Optical Specification - Hardware	
Insertion Loss	≤ 0.25 dB

Connector Specs	
Polish	UPC

Centrix™ XL Splice Cassette 48 Fiber, LC UPC, Single-mode (OS2), Single Fiber



Connector Specs

Connector Type	LC
----------------	----

Dimensions

Height	14 mm (0.55 in)
Width	403 mm (15.87 in)
Depth	290 mm (11.42 in)

Ordering Information

Product Number	CTXLCPP48-A9-2RH000
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.