


Centrix™ loaded housing 1U, 3 cassettes, 24xSC/APC adapters + SF pigtails, 72 ports, HS


CORNING

Part Number:
CX172P24-6C-2RH000

A Centrix™ System 4U housing holds 12 cassettes. Housings can be ordered with cassettes for on-frame splicing. At the foundation of the Centrix System is a single, modular cassette that can be tailored to include a variety of optical devices (splitter, WDM, etc). The modular cassette provides flexibility and functionality within a single frame without sacrificing density. Each cassette contains up to either 24 SC or 36 LC connector adapters. Easy port access is possible due to a sliding cassette with drop-down handle.




Centrix™ loaded housing, 1U, 3 cassettes, 24xSC/APC adapters + SF pigtails, 72 ports, HS



Centrix™ loaded housing, 1U, 3 cassettes, 24xSC/APC adapters + SF pigtails, 72 ports, HS

Centrix™ loaded housing 1U, 3 cassettes, 24xSC/APC adapters + SF pigtails, 72 ports, HS



Specifications

General Specifications	
Product Type	Housings
Fiber Category	Single-mode (OS2)
Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Environmental Conditions	
Temperature Range, Operation	-40 °C to 70 °C (-40 °F to 158 °F)
Design	
Pigtail Type	900 μm
Number of Ports	72

Centrix™ loaded housing 1U, 3 cassettes, 24xSC/ APC adapters + SF pigtails, 72 ports, HS

CORNING

Specifications - Connector A

Connector Type	SC
Polish	APC

Specifications - Connector B

Connector Type	SC
Polish	APC

Dimensions

Height	445 mm (17.52 in)
Width	340 mm (13.39 in)
Depth	290 mm (11.42 in)
Weight	3.5 kg

Ordering Information

Product Number	CX172P24-6C-2RH000
Height Unit	1 U
Shipping Weight	4 kg
Shipping Height	55 cm
Shipping Width	350 cm
Shipping Depth	530 cm
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.