

Evolv® SST-Drop™ with Pushlok® Technology 2F Pushlok to 2F Inline, Toneable, 50 ft, bulk packaging

CORNING

Part Number:
D14802EB1TD050F

As an industry leader in optical connectivity products, Corning designs and manufactures the SST-Drop™ cable assembly with factory-terminated, environmentally sealed and hardened connectors to reduce the cost and the time of drop cable deployment in optical access networks. The Pushlok® drop cable assembly is specifically designed to significantly reduce required drop cable installation.

Features and Benefits

Hardened connector technology

Reduced-diameter Pushlok® connector

Flexible connector offerings

2 & 4 Multifiber drops including pigtail small cell and inline variants available 2F small cell variants with a Pushlok hardened connector to LC or Uniboot

Versatile installation environments

Dielectric and toneable variants available



Evolv® SST-Drop™ with Pushlok® Technology, 2F PushLok to 2F Inline, Toneable, 50 ft, bulk packaging

Evolv® SST-Drop™ with Pushlok® Technology 2F

Pushlok to 2F Inline, Toneable, 50 ft, bulk packaging

CORNING

Specifications

General Specifications

Cable Type	SST-Drop™ toneable
Assembly Insertion Loss	≤ 0.4 dB
Connector Assembly Type	Pushlok Inline
Packaging	Bulk Pack

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Fiber Count	2
-------------	---

Optical Characteristics

Fiber Code	E
Performance Option Code	01
Fiber Category	OS2
Fiber Type	Single-mode (OS2) / 250 µm
Fiber Name	Single-mode (OS2)
Maximum Attenuation	0.4 dB/km / 0.4 dB/km / 0.3 dB/km
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Compliance	ITU-T G.652.D

Specifications - Connector A

Insertion Loss, Max.	0.4 dB
Connector Type	Pushlok
Reflectance	≤ -65 dB

Evolv® SST-Drop™ with Pushlok® Technology 2F Pushlok to 2F Inline, Toneable, 50 ft, bulk packaging

CORNING

Specifications - Connector B

Insertion Loss, Max.	0.4 dB
Connector Type	Inline
Reflectance	≤ -65 dB

Dimensions

Length	50 ft
--------	-------

Ordering Information

Product Number	D14802EB1TD050F
Packaging Method	Box



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.