

# Evolv® Terminal with Pushlok® Technology 6 port, 2x4 body, preconnectorized stub, SST Dielectric, 10 ft

CORNING

**Part Number:**  
**DFB3F1FDD1M1010F0P**

Pushlok® hardened connector technology is the key component enabling smaller terminals for FTTx networks than ever before. Designed for use in nearly every access network environment, the terminal is small enough to be placed in existing handholes or pedestals where space is paramount, on building facades, or in aerial networks (pole- or strand-mount). Improved aesthetics improve end-user adoption for facade applications. There are two styles of terminals designed to meet various space and density requirements: terminals with one row of adapter ports and terminals with two rows of adapter ports. For terminals with one row of adapter ports, the ports are aligned in a single row with the input stub on the left and 2-, 4-, 6- or 8-distribution ports on the right. For terminals with two rows of ports, the input stub is on the front left of the terminal and there are 6-, 8-, 12- or 16- distribution ports. Each port's corresponding release button is actuated to remove the dust cap or drop. When installing drops, the keyed ports provide an audible and physical positive feedback minimizing technician variation and potential damage due to mishandling.

## Features and Benefits

### **Pushlok™ cable assembly connector ports for customer drop terminations**

Lower installation cost and increased speed of connection

### **Standard and integrated splitter terminal options**

#### **Durability**

Solution supports various architecture types

#### **Durability**

100 lb cable tensile strength

### **Available stubbed or preterminated with OptiTip® multifiber connector technology**

Compatible with existing FlexNAP™ installations

### **Small form factor optimizes space in pedestals/handholes**


Lower profile overall with drop entry ports on bottom

### **Ultrasonically welded housing**

Eliminates water ingress potential and prevents unwanted entry in the field

### **Factory-terminated polished connectors**

Eliminates loss associated with excess fusion splices



Evolv® Terminal with Pushlok® Technology, 6 port, 2 rows of 3 ports, preconnectorized OptiTip® stub, SST Dielectric, 10 ft

# Evolv® Terminal with Pushlok® Technology 6 port, 2x4 body, preconnectorized stub, SST Dielectric, 10 ft



## Specifications

| General Specifications              |  |
|-------------------------------------|--|
| Product Type                        | Terminals  |
| Environment                         | Outdoor  |
| Cable Type                          | SST Flat Dielectric Drop                                 |
| Fiber Category                      | ITU-TG.652.D (OS2)                                       |
| Packaging                           | Individual Pack  |
| Preconnectorized "Stubbed" Hardware | Yes  |
| Lockable                            | No   |
| Mounting Type                       | Strand mount, Pole-mount, Pedestal mount, Handhole Mount |
| Splice option                       | No   |
| Application                         | FTTx   |

| Standards |   |
|-----------|---|
| RoHS      | Free of hazardous substances according to RoHS 2011/65/EU |

| Environmental Conditions     |                                     |
|------------------------------|-------------------------------------|
| Temperature Range, Operation | -40 °C to 85 °C (-40 °F to 185 °F ) |
| Temperature Range, Storage   | -40 °C to 85 °C (-40 °F to 185 °F ) |

| Design   |  |
|--|--|
| Fiber Count                                    | 6  |
| Input Fiber Count                              | 6  |
| Fiber Coloring                                 | Blue, Orange, Green, Brown, Slate, White |
| Fibers per Port                                | 1  |
| Number of single-fiber ports, SC APC connector | 6  |
| Housing Material                               | Plastic                                  |

# Evolv® Terminal with Pushlok® Technology 6 port, 2x4 body, preconnectorized stub, SST Dielectric, 10 ft



| Design                    |                          |
|---------------------------|--------------------------|
| Pigtail Length            | 10 ft                    |
| Adapter Type Master Level | Plastic                  |
| Adapter Color Front       | Black                    |
| Adapter Type Front        | Pushlok®                 |
| Housing Type              | Outdoor                  |
| Input Cable Type          | SST Flat Dielectric Drop |
| Locking Availability      | No                       |
| Sealing Type              | Welded                   |
| Housing Color             | Black                    |
| Color                     | Black                    |
| Product Family            | Evolv®                   |
| Number of Ports           | 6                        |

| Design - Adapter |          |
|------------------|----------|
| Housing Color    | Black    |
| Housing Material | Plastic  |
| Adapter Style    | APC      |
| Adapter Type     | Pushlok® |

| Mechanical Specifications |                 |
|---------------------------|-----------------|
| Cold Mate/Demate          | -40 °C (-40 °F) |
| Cable Length              | 10 ft           |

| Optical Specification - Hardware |        |
|----------------------------------|--------|
| Module Insertion Loss, Max       | 0.5 dB |
| Reflectance, Maximum             | 65 dB  |

# Evolv® Terminal with Pushlok® Technology 6 port, 2x4 body, preconnectorized stub, SST Dielectric, 10 ft

CORNING

## Connector Specs

|                  |         |
|------------------|---------|
| Polish           | APC     |
| Housing Color    | Black   |
| Housing Material | Plastic |

## Specifications - Connector A

|                      |          |
|----------------------|----------|
| Connector Type       | Pushlok® |
| Polish               | APC      |
| Insertion Loss, Max. | 0.5 dB   |

## Dimensions

|        |                   |
|--------|-------------------|
| Length | 10 ft             |
| Height | 329 mm (12.95 in) |
| Width  | 2.3 mm (0.09 in)  |
| Depth  | 606 mm (23.86 in) |
| Weight | 0.86 kg           |

## Ordering Information

|                    |                    |
|--------------------|--------------------|
| Product Number     | DFB3F1FDD1M1010F0P |
| Packaging Method   | Box                |
| Units per Delivery | 1/1                |
| Shipping Height    | 30 mm (1.18 in)    |
| Shipping Width     | 30 mm (1.18 in)    |
| Shipping Depth     | 598 mm (23.54 in)  |



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)