

EDGE™ Adapter Panel, MTP® 24 F, 50 µm multimode (OM4), violet

CORNING

Part Number: EDGE-CP24-Q6

EDGE™ MTP® adapter panels provide a simple interface to mate MTP Connectors. This occurs when connecting MTP trunks to MTP extended trunks, MTP trunks to trunk harnesses and, in 40G multimode networks, connecting MTP trunks to 40G patch cords.

Features and Benefits

Provide MTP connection points

Between trunks and harnesses or extender trunks

Installation


Can be installed or removed from the front or rear of a housing

Network upgrades

Facilitate simple upgrades to parallel optics

Packaging

Packaged in easy-open containers



EDGE™ Adapter Panel, MTP®, 24 F, 50 µm multimode (OM4), violet

EDGE™ Adapter Panel, MTP® 24 F, 50 µm multimode (OM4), violet

CORNING

Specifications

General Specifications

Fiber Category	50 µm MM (OM4)
----------------	----------------

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Number of Adapters per Panel	2
Fiber Count	24

Design - Adapter

Housing Color	Violet
Housing Material	Composite
Adapter Style	Standard
Adapter Type	MTP®

Dimensions

Height	9 mm (0.35 in)
Width	100 mm (3.94 in)
Depth	125 mm (4.92 in)
Weight	25 g

Ordering Information

Product Number	EDGE-CP24-Q6
Shipping Weight	220 g
Shipping Height	200 mm (7.87 in)

EDGE™ Adapter Panel, MTP® 24 F, 50 µm multimode (OM4), violet



Ordering Information	
Shipping Width	250 mm (9.84 in)
Shipping Depth	130 mm (5.12 in)
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.