

# EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Straight-through Polarity (TIA)



**Part Number:**  
**ETM-5B-G-S**

EDGE™ Tap module for traditional LC duplex systems enables the customer to manage the monitoring access points via the patch cord infrastructure zone at the front of the cabinets.


## Features and Benefits

Designed for Duplex based infrastructure solutions


### Utilizes advanced splitter technology

Maintains equal modal power distribution, reducing insertion loss for increased link reach

EDGE Solutions-based footprint



EDGE™ Solutions Tap Module, Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Straight-through Polarity (TIA Type A)



EDGE™ Solutions Tap Module, Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Straight-through Polarity (TIA Type A)

**EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Straight-through Polarity (TIA**



**Specifications**

General Specifications	
Product Type	Modules
Fiber Category	Single-mode (OS2)
Mounting Type	Rack Mount
Application	Data Center LAN/SAN

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Design	
Adapter Type Back	MTP®
Adapter Color Back	Black / Red
Adapter Color Front	Blue
Adapter Type Front	Shuttered LC
Housing Type	Modules
Number of Ports	12
Number of Adapters per Panel	6

Cable Design	
Polarity	Straight-Through, TIA-568 Type-A

Connector Specs	
Connector Type	LC

Specifications - Connector A	
Connector Type	LC Duplex

**EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), 12 F LC duplex ports, one pinned MTP® adapter labeled LIVE, one pinned red MTP adapter labeled TAP, enables six monitored ports, Straight-through Polarity (TIA**



**Specifications - Connector A**

Ferrule Material	Ceramic
------------------	---------

**Specifications - Connector B**

Connector Type	MTP® (pinned)
Ferrule Material	Ceramic

**Dimensions**

Weight	16 kg
Length	0 mm (0 in)

**Ordering Information**

Product Number	ETM-5B-G-S
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)